

F

E

D

C

B

A

F








E

D

C


B

A



SPECIFICATIONS:

1. CONTACT RESISTANCE: 20 mΩ MAX
2. INSULATION RESISTANCE: 100 mΩ MIN. AT 250V DC.
3. DIELECTRIC STRENGTH: 250V AC 1 MINUTE.
4. LIFE TEST: JACK SHALL WITHSTAND 5000 CYCLES OF INSERTION AND WITHDRAWAL WITH TESTING PLUG, AFTER TEST THE CONTACT RESISTANCE SHALL NOT EXCEED 0.1 Ω
5. MEASURING CONDITION: TEMPERATURE FORM 5°C TO 35°C
RELATIVE HUMIDITY FOR 40% TO 85%.
6. INSERTION FORCE: 0.4Kg~1.6Kg.
7. WITHDRAWAL FORCE: 0.4Kg~1.2Kg.



CIRCUIT DIAGRAM

CUSTOMER DRAWING

						★ STAR SYMBOL DENOTES CRITICAL DIMENSION UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PALCE DECIMALS ±0.005 - FRACTIONAL DIMENSIONS ±1/64 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS DO NOT SCALE DRAWING	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
							SIZE	WIDTH	MULT	LBS/M	TEMPER	
							FINISH SPEC No.			MATERIAL SPEC No.		
							FIRST USED ON			SCALE 4.000		
B	ECO #20278	11-5-96	MM	JC			DATE DRAWN 28-Oct-93	BY LR	CHKD LR	APVD JC	Switchcraft® SHEET OF 35RAPC2AV REV B	
A	FIRST DRAWN	10-28-93	LR	JC								
REV	ECO NUMBER	DATE	BY	APVD		NAME 3.5 MM MONO JACK						
REVISIONS												