



番号 (NUMBER)
C-170053

△ OBSOLETE 1-170053-7 黄銅 0.5t 半田めっき 7.52 4.34



BRASS

TIN-LEAD PL.



断面 A-A
SECT

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



断面 B-B
SECT

△ OBSOLETE

L.P. TERMINAL DN バラ状端子型番	S.T. TERMINAL DN 連鎖状端子型番	MATERIAL 材 料	FINISH 仕 上	"E" ±0.15	"H" ±0.1
170053-1	170011-1	黄銅 0.5t	—	7.52	5.0
↑	↑	BRASS	錫めっき		5.0
-2			—		4.19
-3			錫めっき		4.19
-4			—		3.2
-5			錫めっき		3.2
-6			—		4.34
-7			錫めっき		4.34
170053-8	170011-8		—		5.2
↑	↑		錫めっき	7.52	5.2
1-170053-1	1-170011-1		—	6.5	4.19
↑	↑		錫めっき		4.19
-2			—		3.68
-3			錫めっき		3.68
-4			—		
-5			錫めっき		
1-170053-6	1-170011-6	黄銅 0.5t	錫めっき	6.5	3.68

B1 ECO-10-000444				KK	AEG	08JAN	材料 (MATERIAL) 表参照 仕上 (FINISH) 表参照 適合電線断面積 (WIRE RANGE) 0.75~2.27 mm ² (AWG #8-14) 被覆外径 (INSULATION DIA) 3.05~4.32 mm (120~170 IN)		参考図面 (CUSTOMER COPY) (REFERENCE ONLY)		
B ADDED 1-7 (FJ00-1596-94)				Y.I	S.M	12-8 '84	AMP		AMP (JAPAN), LTD. Tokyo, Japan		
A1 OBSOLETE (FJ00-0525-93)				K.N	Y.T	7-23 '93	分類 (CLASS)		丸型 RING TONGUE		
A REVISED PER ECN				H.O	H.O	10/23 '82	型式 (TYPE)		—		
O RELEASED				H.O	K.M	4/21/85	一般公差 (TOLERANCE) EXCEPT (AS NOTED) ±0.4 ±1.0		尺度 (SCALE) 4-1 LOC J SIZE A 番号 (NO) C-170053 REV B1		
LTR 変更 (REVISION RECORD)				DR	CHK	DATE	名称 (NAME) RING TONGUE TERMINAL L.P. 丸型端子 (バラ状)				
DR 4-21 '75				DE		15/12/75					
CHK 5/13/75 APP				Y. Sato		5/19/75					