







4

3

2


1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DY	-		A	REVISED PER	21FEB2012	I.T	S.Y



NOTES:

- MATERIALS:
HOUSING: L.C.P (HIGH TEMP THERMO PLASTIC) UL 94V-0, NATURAL.
CONTACT: COPPER ALLOY.
- FINISH:
ENGAGEMENT AREA: 0.00076 MIN GOLD
SOLDERING AREA: 0.002 MIN MATTE TIN
UNDERCOAT: 0.0013 MIN NICKEL
ALL OVER
- POSITION SERIES:
SEE P/N TABLE ON SHEET 2.
- CONNECTOR MATED STACKED HEIGHT IS COMBINATION OF PLUG HEIGHT "Y" AND REC HEIGHT "X", LESS 5 mm.
 $STACKED\ HEIGHT = Y + X - 5$



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN IVAN TIAN 21FEB2012	TE Connectivity			
		CHK WENKE HE 29MAR2012				
		APVD STEVEN YAO 29MAR2012	NAME FH 0.8mm BTB CONNECTOR RECEPTACLE 19mm HEIGHT WITH STEEL COVER, ON EMBOSS TAPE			
DIMENSIONS: mm		PRODUCT SPEC 108-5390	SIZE A300779			
		APPLICATION SPEC 114-5254	CAGE CODE C-2199039			
MATERIAL 		WEIGHT -	RESTRICTED TO -			
		FINISH SEE P/N TABLE	SCALE 1:1			
		Customer Drawing	SHEET 1 OF 2			
			REV A			

