


Distributed by:

JAMECO[®]
ELECTRONICS



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.


Jameco Part Number 151590

SCHEMATIC	
MODEL NO	C




M13-P1.0 METRIC THREAD



Date	Rev.	Description



NUT



Pin Hole Layout
(Jack Bottom View)

7.	Nut	2.3T Brass	1	Nickel Plated
6.	Insulator	1.0T Bakelite	1	Natural
5.	Housing	POM	1	Black
4.	Pin(2.0φ)	Copper	1	Nickel Plated
3.	Break Terminal	0.3T Brass	1	Silver Plated
2.	Sleeve Spring	0.2T Phosphor Bronze	1	Silver Plated
1.	Pin Terminal	0.4T Brass	1	Silver Plated
NO.	Description	Material	Q'TY	Finish

SPECIFICATIONS:

Contact Resistance : 30mΩ max
Insulation Resistance : 100MΩ min. at DC 500V
Dielectric Withstand Voltage: AC 500V for one minute
Remark: ▲: The Most Important Dimension

DCC. NO.
A4 DRAWING NO.

MATERIAL	GOLDSUN ELECTRONICS CO., LTD.			
JAMECO NO.	151590	GOLDSUN NO.	SCD522CCS100B00G	
DRAWN: Kiki Chen	Description			Rev.
VERIFY PEOPLE: Ada Zheng, Ivy Lan	POWER JACK, LEAD WIRE			1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No:	ERN No: