


CUSTOMER:
CUSTOMER PN:
GPN: E74D400LPN113UC79M

DRAWING NO.: 436831

ELECTRICAL CRITERIA

CAPACITANCE (120Hz/25°C): 11000 μ F

CAPACITANCE TOLERANCE: -10/+75 %

RATED V_{DC} 40 V

SURGE V_{DC} (30 sec): 50 V

MAX. ESR (120Hz/25°C): 17 m Ω

MAX. I_{RMS} (120Hz/85°C): 16.8 A

MAX. DCL (V_{DC}/5:00/25°C): 1.000 mA

MECHANICAL CRITERIA

MAX. VIBRATION: 10-55Hz 10g

TERMINAL THREAD 10-32

THREAD DEPTH 5.6 mm

MAX. TERMINAL TORQUE: 2 Nm

TYP. WEIGHT: 213 grams

OPERATING CRITERIA

MAX. TEMPERATURE: +105 °C

MIN. TEMPERATURE: -55 °C

LOAD LIFE (V_{DC}/105°C): 2000 Hrs

MAX. Δ CAP. (measured value): $\pm$ 20 %

MAX. ESR (specified value): $\leq$ 150 %

MAX. DCL (V_{DC}/5:00/25°C): 1.000 mA

SHELF LIFE (85°C): 1000 Hrs

MAX. Δ CAP. (measured value): $\pm$ 15 %

MAX. ESR (specified value): $\leq$ 130 %

MAX. DCL (V_{DC}/5:00/25°C): 2.000 mA

I_{RMS} FREQUENCY MULTIPLIERS

120Hz	400Hz	1kHz	5k-100kHz
0.90	0.95	0.98	1.00

I_{RMS} AMBIENT MULTIPLIERS

25°C	45°C	65°C	85°C	105°C
2.00	1.70	1.40	1.00	0.50

SPECIAL

RoHS Compliant

ISSUE: 2 DATE: 11/2/09

DIMENSIONAL CRITERIA

	mm	X	in
$\varnothing$ D	2.000	- 0.040	+ 0.040
L	3.125	- 0.080	+ 0.080
H	3.188	- 0.080	+ 0.080
F	0.875	- 0.016	+ 0.016
J	0.063	- 0.040	+ 0.040
$\varnothing$ S	0.313	- 0.010	+ 0.010



MARKING


747D 105°C

11000uF 40V

Date Code

+ positive



TDS NO.: TDS-11-0040-02

AUTHOR: TMASH

DATE: 04-JAN-2017

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[United Chemi-Con \(UCC\):](#)

[E74D400LPN113UC79M](#) [747D812M035AA2B](#) [E74D400LPN422UA41M](#) [747D383M016AB2A](#) [747D223M045BC2A](#)
[747D233M025AB2AEA](#)