

## MLG1005S2N0ST000

Applications		Commercial Grade
Feature	<b>Multilayer</b>  Non-Magnetic Core (Dielectric Ceramic)	Multilayer
Series	MLG Series / MLG1005S Type	
Status	PROD	



Size	
Length(L)	1.00mm +/-0.05mm
Width(W)	0.50mm +/-0.05mm
Thickness(T)	0.50mm +/-0.05mm
Recommended Land Pattern (A)	0.50mm Nom.
Recommended Land Pattern (B)	0.40mm Nom.
Recommended Land Pattern (C)	0.50mm Nom.

Electrical Characteristics	
Inductance	2nH +/-0.3nH at 100MHz
Rated Current (Temperature Rise) [Max.]	900mA (20degC Rise)
Self-Resonant Frequency [Min.]	7.5GHz
Self-Resonant Frequency [Typ.]	9.3GHz
Q [Min.]	7 at 100MHz
Q [Typ.]	11 at 100MHz
DC Resistance [Nom.]	70mΩ
DC Resistance [Max.]	150mΩ


Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	10000Pcs Min.
Weight	0.001g

•This PDF document was created based on the data listed on the TDK Corporation website.


•All specifications are subject to change without notice.

## MLG1005S2N0ST000


**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)




MLG1005S2N0ST000



MLG1005S2N0ST000





MLG1005S2N0ST000




MLG1005S2N0ST000

## MLG1005S2N0ST000

### Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



MLG1005S2N0ST000(Amb. Temp. = 20degC)



- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.