

2,000 V - 15,000 V Rectifiers

50 mA - 420 mA Forward Current

30 ns - 50 ns Recovery Time

X20FF3 - X150FF3

X20FF5 - X150FF5

AXIAL LEADED

HERMETICALLY SEALED




4

ELECTRICAL CHARACTERISTICS AND MAXIMUM RATINGS

Part Number	Working Reverse Voltage	Average Rectified Current		Reverse Current @ Vrwm		Forward Voltage		1 Cycle Surge Current tp=8.3ms (Ifsm)	Repetitive Surge Current (Ifrm)	Reverse Recovery Time (3) (Trr)	Thermal Impedance			Junction Cap. @50VDC @ 1kHz (Cj)
	(Vrwm)	(Io)		(Ir)		(Vf)					θ_{J-L}			
	Volts	55°C(1)	100°C(2)	25°C	100°C	25°C	25°C	25°C	25°C	25°C	L=.000	L=.125	L=.250	25°C
		mA	mA	µA	µA	Volts	mA	Amps	Amps	ns	°C/W	°C/W	°C/W	pF
X20FF3	2000	420	210	1.0	20	7.5	420	16.0	3.0	30	5	12	21.5	4.0
X50FF3	5000	150	75	1.0	20	12.5	150	10.0	1.0	30	5	12	21.5	3.0
X100FF3	10000	80	40	1.0	20	25.0	80	2.0	0.5	30	5	12	21.5	2.0
X150FF3	15000	50	25	1.0	20	37.5	50	1.6	0.3	30	5	12	21.5	2.0
X20FF5	2000	420	210	1.0	20	7.5	420	16.0	3.0	50	5	12	21.5	4.0
X50FF5	5000	150	75	1.0	20	12.5	150	10.0	1.0	50	5	12	21.5	3.0
X100FF5	10000	80	40	1.0	20	25.0	80	2.0	0.5	50	5	12	21.5	2.0
X150FF5	15000	50	25	1.0	20	37.5	50	1.6	0.3	50	5	12	21.5	2.0

(1)TL=55°C L=0.375" (2)TL=100°C L=0.375" (3)If=125mA, Ir=250mA, Irr=63mA • Op. Temp.= -65°C to +175°C Stg.Temp.= -65°C to +200°C



Dimensions: In. (mm) • All temperatures are ambient unless otherwise noted. • Data subject to change without notice.



VOLTAGE MULTIPLIERS INC.
8711 W. Roosevelt Ave.
Visalia, CA 93291

TEL 559-651-1402
FAX 559-651-0740
www.voltagemultipliers.com

X20FF3 - X150FF3 X20FF5 - X150FF5

