CR1632

3V Lithium Battery
Swiss Made

Technical Data Sheet

Specifications

Chemical System	Li / MnO_2
Nominal Voltage	3 V
Rated Capacity	125 mAh
Standard Discharge Current	0.2 mA
Max. Cont. Discharge Current	1.5 mA
Average Weight	1.8 g
Operating Temperature*	-40 - +85 °C
Self Discharge at 23°C	< 1% / year

Dimensions



Performance

Discharge performance at 23°C



Discharge performance at 23°C



Temperature performance Load 16.2kΩ



Cell capacity at various loads



In applications where the battery is exposed to temperatures above 70 °C, please contact Renata for consultancy.

Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.

Rev. CR1632.06 / 12.06

Renata SA
CH-4452 Itingen/Switzerland
Tel. +41 (0)61 975 75 75
Fax. +41 (0)61 975 75 95
sales@renata.com
www.renata.com

A COMPANY OF THE SWATCH GROUP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Renata:

CR1632.IB 400/CASE