

NOTES:

MATERIAL:
HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.
TERIMINAL: BRIGHT TIN PLATED, COPPER ALLOY.
SCREW: 6-32, STEEL, ZINC PLATED CLEAR CHROMATE.






ELECTRICAL:

UL CLASS	C:	20A,	150V.
UL CLASS	D:	10A,	300V.
CSA TYPE	B:	20A,	300V.
CSA TYPE	C:	20A,	300V.
CSA TYPE	D:	10A,	300V.
CSA TYPE	E:	20A,	300V.

WIRE RANGE: 12-22 AWG


MECHANICAL:
MAXIMUM TORQUE RATING: 7 IN-LBS.
RUNNING TORQUE: 0.5-3.5 IN-LBS UNLESS
OTHERWISE STATED.

- | | |
|---|---|
| 1 | SCREWS ARE BOTTOMED, NO THREAD INTERRUPT. |
| 2 | SCREWS ARE NICKEL PLATED BRASS. |
| 3 | SCREWS ARE CAPTIVE. |
| 4 | SEE FIGURE. |
| 5 | PRELIMINARY PART NUMBER. |
| 6 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |
| 7 | TERMINAL FINISH: MATTE TIN |
| 8 | OBSOLETE |



2-796658-4

MATERIAL		DESCRIPTION		QTY	UNIT	PART NUMBER		
8	5	.160	4DB-P108-04-SPCL	1.365	4	3-796658-0		
	8	5	.160	4DB-P108-03-SPCL	1.040	3	2-796658-9	
8		.160	4DB-P108-30	9.815	30	5-1437667-5		
8		.160	4DB-P108-29	9.490	29	796658-9		
8		.160	4DB-P108-28	9.165	28	5-1437667-3		
8		.160	4DB-P108-27	8.840	27	796658-8		
8		.160	4DB-P108-26	8.515	26	5-1437667-2		
8		.160	4DB-P108-25	8.190	25	796658-7		
8		.160	4DB-P108-24	7.865	24	5-1437667-0		
8		.160	4DB-P108-23	7.540	23	796658-6		
8		.160	4DB-P108-22	7.215	22	4-1437667-8		
	8	.160	4DB-P108-21	6.890	21	796658-2		
8		.160	4DB-P108-20	6.565	20	4-1437667-6		
8		.160	4DB-P108-19	6.240	19	4-1437667-5		
8		.160	4DB-P108-18	5.915	18	4-1437667-4		
8	5	4	.160	4DB-P108-16-105	5.590	17	2-796628-4	
8		.160	4DB-P108-17	5.590	17	4-1437667-2		
8		.160	4DB-P108-16	5.265	16	4-1437667-0		
	8	.160	4DB-P108-15	4.940	15	3-1437667-9		
2	1	.160	4DB-P108-14-102	4.615	14	2-796658-5		
2		.160	4DB-P108-14-102	4.615	14	2-796658-3		
		.160	4DB-P108-14	4.615	14	3-1437667-8		
		.160	4DB-P108-13	4.290	13	3-1437667-7		
		.160	4DB-P108-12	3.965	12	3-1437667-6		
		.160	4DB-P108-11	3.640	11	3-1437667-5		
		.160	4DB-P108-10	3.315	10	3-1437667-3		
8	5	2	.160	4DB-P106-09-094	2.990	9	1-796658-7	
		.160	4DB-P108-09	2.990	9	3-1437667-2		
6	1	OBSOLETE	.160	4DB-P108-08-091	2.665	8	1-796658-4	
		.160	4DB-P108-08	2.665	8	3-1437667-1		
8	5	3	2	.160	4DB-P106-07-100	2.340	7	2-796658-2
		.160	4DB-P106-07-093	2.340	7	1-796658-6		
		.160	4DB-P108-07	2.340	7	3-1437667-0		
8	5	3	2	.160	4DB-P106-06-099	2.015	6	2-796658-1
6	1	OBSOLETE	.160	4DB-P108-06-090	2.015	6	1-796658-3	
8	5		.200	4DB-P108-06	2.015	6	2-796658-6	
		.160	4DB-P108-06	2.015	6	2-1437667-9		
8	5	3	2	.160	4DB-P106-05-098	1.690	5	2-796658-0
6	4	OBSOLETE	.160	4DB-P108-05-093	1.690	5	1-796658-5	
		.160	4DB-P108-05	1.690	5	2-1437667-8		
8	5	3	2	.160	4DB-P106-04-097	1.365	4	1-796658-9
	1	.160	4DB-P108-04-089	1.365	4	1-796658-2		
		.160	4DB-P108-04	1.365	4	2-1437667-6		
8	5	3	2	.160	4DB-P106-03-096	1.040	3	1-796658-8
6	1	.160	4DB-P108-03-088	1.040	3	1-796658-1		
		.160	4DB-P108-03	1.040	3	2-1437667-5		
7		.142	4DB-P108-02-143	.715	2	2-796658-8		
		.142	4DB-P108-02-142	.715	2	2-796658-7		
		.160	4DB-P108-02	.715	2	2-1437667-4		
		DIM B	CATALOG NUMBER	DIM A	NO OF POS.	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S WELDON		01MAY2003		 TE Connectivity	
		CHK S YODER		5/1/03			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S YODER		NAME	
		0 PLC ± -		PRODUCT SPEC		ASSEMBLY, DUAL BARRIER 4DB P108 XX	
		1 PLC ± -		—			
		2 PLC ± .01		APPLICATION SPEC			
		3 PLC ± .005		—			
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
-		-		—		—	
CUSTOMER DRAWING				SCALE		SHEET	
				N.TS		1 of 1	
						REV N8	