



NDC652P P-Channel Logic Level Enhancement Mode Field Effect Transistor

General Description

These P-Channel logic level enhancement mode power field effect transistors are produced using Fairchild's proprietary, high cell density, DMOS technology. This very high density process is especially tailored to minimize on-state resistance. These devices are particularly suited for low voltage applications such as notebook computer power management and other battery powered circuits where fast high-side switching, and low in-line power loss are needed in a very small outline surface mount package.

Features

- -2.4A, -30V. $R_{DS(ON)} = 0.18\Omega$ @ $V_{GS} = -4.5V$
 $R_{DS(ON)} = 0.11\Omega$ @ $V_{GS} = -10V$.
- Proprietary SuperSOT™-6 package design using copper lead frame for superior thermal and electrical capabilities.
- High density cell design for extremely low $R_{DS(ON)}$.
- Exceptional on-resistance and maximum DC current capability.



Absolute Maximum Ratings

$T_A = 25^\circ C$ unless otherwise noted

Symbol	Parameter	NDC652P	Units
V_{DSS}	Drain-Source Voltage	-30	V
V_{GSS}	Gate-Source Voltage - Continuous	-20	V
I_D	Drain Current - Continuous	-2.4	A
	- Pulsed	-10	
P_D	Maximum Power Dissipation (Note 1a)	1.6	W
	(Note 1b)	1	
	(Note 1c)	0.8	
T_J, T_{STG}	Operating and Storage Temperature Range	-55 to 150	°C
 THERMAL CHARACTERISTICS			
R_{QJA}	Thermal Resistance, Junction-to-Ambient (Note 1a)	78	°C/W
R_{QJC}	Thermal Resistance, Junction-to-Case (Note 1)	30	°C/W

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)						
Symbol	Parameter	Conditions	Min	Typ	Max	Units
OFF CHARACTERISTICS						
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{\text{GS}} = 0 \text{ V}$, $I_{\text{D}} = -250 \mu\text{A}$	-30			V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{\text{DS}} = -24 \text{ V}$, $V_{\text{GS}} = 0 \text{ V}$			1	μA
		$T_J = 55^\circ\text{C}$			10	μA
I_{GSSF}	Gate - Body Leakage, Forward	$V_{\text{GS}} = 20 \text{ V}$, $V_{\text{DS}} = 0 \text{ V}$			100	nA
I_{GSSR}	Gate - Body Leakage, Reverse	$V_{\text{GS}} = -20 \text{ V}$, $V_{\text{DS}} = 0 \text{ V}$			-100	nA
ON CHARACTERISTICS (Note 2)						
$V_{\text{GS(th)}}$	Gate Threshold Voltage	$V_{\text{DS}} = V_{\text{GS}}$, $I_{\text{D}} = -250 \mu\text{A}$	-1	-1.5	-3	V
		$T_J = 125^\circ\text{C}$	-0.7	-1.2	-2.2	
$R_{\text{DS(ON)}}$	Static Drain-Source On-Resistance	$V_{\text{GS}} = -4.5 \text{ V}$, $I_{\text{D}} = -2.4 \text{ A}$		0.16	0.18	Ω
		$T_J = 125^\circ\text{C}$		0.22	0.36	
		$V_{\text{GS}} = -10 \text{ V}$, $I_{\text{D}} = -3.1 \text{ A}$		0.09	0.11	
$I_{\text{D(on)}}$	On-State Drain Current	$V_{\text{GS}} = -4.5 \text{ V}$, $V_{\text{DS}} = -5 \text{ V}$	-5			A
g_{FS}	Forward Transconductance	$V_{\text{DS}} = -10 \text{ V}$, $I_{\text{D}} = -2.4 \text{ A}$		3		S
DYNAMIC CHARACTERISTICS						
C_{iss}	Input Capacitance	$V_{\text{DS}} = -15 \text{ V}$, $V_{\text{GS}} = 0 \text{ V}$, $f = 1.0 \text{ MHz}$		290		pF
C_{oss}	Output Capacitance			180		pF
C_{rss}	Reverse Transfer Capacitance			60		pF
SWITCHING CHARACTERISTICS (Note 2)						
$t_{\text{D(on)}}$	Turn - On Delay Time	$V_{\text{DD}} = -15 \text{ V}$, $I_{\text{D}} = -1 \text{ A}$, $V_{\text{GEN}} = -4.5 \text{ V}$, $R_{\text{GEN}} = 6 \Omega$		13	20	ns
t_r	Turn - On Rise Time			26	35	ns
$t_{\text{D(off)}}$	Turn - Off Delay Time			22	30	ns
t_f	Turn - Off Fall Time			19	30	ns
Q_g	Total Gate Charge	$V_{\text{DS}} = -15 \text{ V}$, $I_{\text{D}} = -2.4 \text{ A}$, $V_{\text{GS}} = -10 \text{ V}$		10.5	20	nC
Q_{gs}	Gate-Source Charge			1.5		nC
Q_{gd}	Gate-Drain Charge			3.3		nC

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
DRAIN-SOURCE DIODE CHARACTERISTICS						
I _S	Continuous Source Diode Current				-1.3	A
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0 V, I _S = -1.3 A (Note 2)		-0.8	-1.2	V


Notes:

1. R_{θJA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. R_{θJC} is guaranteed by design while R_{θCA} is determined by the user's board design.

$$P_D(t) = \frac{T_J - T_A}{R_{θJ} k(t)} = \frac{T_J - T_A}{R_{θJ} + R_{θCA}(t)} = I_D^2(t) \times R_{DS(on)} \theta T_J$$

Typical R_{θJA} using the board layouts shown below on 4.5" x 5" FR-4 PCB in a still air environment:

- 78°C/W when mounted on a 1 in² pad of 2oz copper.
- 125°C/W when mounted on a 0.01 in² pad of 2oz copper.
- 156°C/W when mounted on a 0.003 in² pad of 2oz copper.



Scale 1 : 1 on letter size paper

2. Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2.0%.

Typical Electrical Characteristics




Figure 1. On-Region Characteristics




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage




Figure 3. On-Resistance Variation with Temperature




Figure 4. On-Resistance Variation with Drain Current and Temperature




Figure 5. Transfer Characteristics




Figure 6. Gate Threshold Variation with Temperature

Typical Electrical Characteristics (continued)




Figure 7. Breakdown Voltage Variation with Temperature




Figure 8. Body Diode Forward Voltage Variation with Source Current and Temperature




Figure 9. Capacitance Characteristics




Figure 10. Gate Charge Characteristics




Figure 11. Switching Test Circuit




Figure 12. Switching Waveforms

Typical Electrical and Thermal Characteristics (continued)




Figure 13. Transconductance Variation with Drain Current and Temperature




Figure 14. SOT-6 Maximum Steady-State Power Dissipation versus Copper Mounting Pad Area.




Figure 15. Maximum Steady-State Drain Current versus Copper Mounting Pad Area.




Figure 16. Maximum Safe Operating Area




Figure 17. Transient Thermal Response Curve.

Note: Thermal characterization performed using the conditions described in note 1c. Transient thermal response will change depending on the circuit board design.

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACE TM	ISOPLANART TM	SyncFET TM
CoolFET TM	MICROWIRE TM	TinyLogic TM
CROSSVOLT TM	POP TM	UHC TM
E ² CMOS TM	PowerTrench [®]	VCX TM
FACT TM	QFET TM	
FACT Quiet Series TM	QST TM	
FAST [®]	Quiet Series TM	
FAST _r TM	SuperSOT TM -3	
GTO TM	SuperSOT TM -6	
HiSeC TM	SuperSOT TM -8	

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.