

BC179	TO-18	25	20 BV _{CES} 25	5	100	20					(V _{CEK}) 0.6	0.6	0.75*	2	6			4 4	1 5	71
BC179A	TO-18	25	20 BV _{CES} 30	5	100	20					(V _{CEK}) 0.6	0.6	0.75*	2	6			4 4	1 5	71
BC179B	TO-18	25	20	5	100	20					(V _{CEK}) 0.6	0.6	0.75*	2	6			4 4	1 5	71
BC182K	TO-106	60	50	5	15	50	40 100 80	0.01 2 100	5 5 5	0.25 0.6				10 100 2	5	150	10	10	1	04
BC182KA	TO-106	60	50	5	15	50	40 100 80	0.01 2 100	5 5 5	0.25 0.6		0.55	0.7*	10 100 2	5	150	10	10	1	04
BC182KB	TO-106	60	50	5	15	50	40 100 80	0.01 2 100	5 5 5	0.25 0.6		0.55	0.7*	10 100 2	5	150	10	10	1	04
BC182L	TO-92 (74)	60	50	5	15	50	40 80 125	0.01 100 500*	5 5 2	0.25 0.6				10 100 2	5	150	10	10	1	04
BC182LA	TO-92 (74)	60	50	5	15	50	40 80 125	0.01 100 260*	5 5 2	0.25 0.6		0.55	0.7*	10 100 2		150	10	10	1	04
BC182LB	TO-92 (74)	60	50	5	15	50	40 80 240	0.01 100 500*	5 5 2	0.25 0.6		0.55	0.7*	10 100 2	5	150	10	10	1	04
BC183K	TO-106	45	30	5	15	30	40 100 80	0.01 2 100	5 5 5	0.25 0.6				10 100 2	5	150	10	10	1	04
BC183KA	TO-106	45	30	5	15	30	40 100 80	0.01 2 100	5 5 5	0.25 0.6		0.55	0.7*	10 100 2	5	150	10	10	1	04
BC183KB	TO-106	45	30	5	15	30	40 100 80	0.01 2 100	5 5 5	0.25 0.6		0.55	0.7*	10 100 2	5	150	10	10	1	04
BC183KC	TO-106	45	30	5	15	30	40 100 80	0.01 2 100	5 5 5	0.25 0.6		0.55	0.7*	10 100 2	5	150	10	10	1	04
BC183L	TO-92 (74)	45	30	5	15	30	40 80 125	0.01 100 900*	5 5 2	0.25 0.6				10 100 2	5	150	10	10	1	04
BC183LA	TO-92 (74)	45	30	5	15	30	40 80 125	0.01 100 260*	5 5 2	0.25 0.6		0.55	0.7*	10 100 2	5	150	10	10	1	04
BC183LB	TO-92 (74)	45	30	5	15	30	40 80 240	0.01 100 500*	5 5 2	0.25 0.6		0.55	0.7*	10 100 2	5	150	10	10	1	04

Test Conditions:		1. I _C = 200 μA, V _{CE} = 5V, R _S = 2 kΩ, f = 1 kHz, BW = 200 Hz	4. I _C = 20 μA, V _{CE} = 5V, R _S = 10 kΩ, f = 1 kHz, BW = 150 Hz	7. I _C = 50 μA, V _{CE} = 5V, R _S = 10 kΩ, BW = 10 Hz to 15 kHz	10. I _C = 10 μA, V _{CE} = 5V, R _S = 10 kΩ, WB	13. I _C = 10 mA, I _{B1} = 3 mA, I _{B2} = 1 mA	16. I _C = 150 mA, V _{CE} = 6V, I _{B1} = I _{B2} = 15 mA	19. V _{CC} = 20V, I _C = 100 mA I _{B1} = I _{B2} = 5 mA
	2. I _C = 200 μA, V _{CE} = 5V, R _S = 2 kΩ, WB	5. I _C = 200 μA, V _{CE} = 5V, R _S = 2 kΩ, f = 20 Hz to 15 kHz	8. I _C = 50 μA, V _{CE} = 5V, R _S = 10 kΩ, f = 1 kHz, BW = 200 Hz	11. I _C = 150 mA, V _{CE} = 10V, I _{B1} = I _{B2} = 15 mA	14. I _C = 100 mA, I _{B1} = 40 mA, I _{B2} = 20 mA	17. I _C = 10 mA, I _{B1} = 1 mA, I _{B2} = -1 mA		
	3. I _C = 30 μA, V _{CE} = 5V, R _S = 10 kΩ, f = 1 kHz, BW = 200 Hz	6. I _C = 100 μA, V _{CE} = 5V, R _S = 2 kΩ, f = 10 Hz to 10 kHz	9. I _C = 200 μA, V _{CE} = 2V, R _S = 2 kΩ, f = 1 kHz, BW = 200 Hz	12. I _C = 150 mA, I _{B1} = I _{B2} = ±7.5 mA	15. V _{CC} = 10V, I _C = 100 mA I _{B1} = I _{B2} = 10 mA	18. I _C = 300 mA, I _{B1} = I _{B2} = 30 mA, V _{CC} = 25V		