

Handheld Megohmmeter



1000V digital tester

With large dual backlit display

Features:

- Double molded housing for added durability
- Dual display of Insulation Resistance and Test Voltage
- Backlit super large display
- 250V, 500V, and 1000V test voltages
- Insulation Resistance to 2000M Ω
- Auto power off
- Lo Ω function for testing connections
- Lock Power On Function for hands-free operation
- Data Hold to freeze displayed reading
- Complete with heavy duty test leads, alligator clip test lead, hanging strap, hard carrying case, and 6 x AA batteries



Measures the insulation resistance of motors



Specifications

Insulation Resistance	200M Ω , 2000M Ω
Max Resolution	0.1M Ω
Basic Accuracy	$\pm 3\%$
Insulation Test Voltages	250V, 500V, 1000V
AC Voltage Test	Yes
Low Resistance Test	Yes
Power source	6 x AA batteries
Dimensions	7.8 x 3.6 x 1.9" (200 x 92 x 50mm)
Weight	24.6oz (700g)

Ordering Information:

380260.....Handheld Megohmmeter
380260-NIST380260 with Calibration Traceable to NIST
TL805.....Double Injected Test Leads



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[380260](#)