

ALPHA WIRE

CUSTOMER PRODUCT SPECIFICATION

Part Number: 78073
Page 1 of 1 Pages

Issue: 1
Issue Date: 7/11/2014
Effective Date: 9/5/2014

A. Construction

Diameters (In)

- | | | |
|----------------|---|-------|
| 1) Component 1 | 3 X 1 PAIR | |
| a) Conductor | 24 (19/36) AWG Tinned Copper | 0.025 |
| b) Insulation | 0.007" Wall, Nom. Modified Polyphenylene Ether-PE | 0.039 |
| (1) Color Code | Alpha Wire Color Code B | |

Pair	Color	Pair	Color	Pair	Color
1	WHITE-BLACK	2	WHITE-BROWN	3	WHITE-RED

- | | | |
|-------------------|---|--------------------|
| c) Pair | 2/Cond Cabled Together | |
| (1) Twists: | 12.0 Twists/foot (min) | |
| 2) Cable Assembly | 3 Components Cabled | |
| a) Twists: | 6.0 Twists/foot (min) | |
| b) Core Wrap | Nonwoven Polyester Tape, 25% Overlap, Min. | |
| 3) Jacket | 0.015" Wall, Nom., Modified Polyphenylene Ether-PE | 0.172 (0.183 Max.) |
| a) Color(s) | SLATE | |
| b) Ripcord | 1 End 810 Denier Nylon | |
| c) Print | ALPHA WIRE-* P/N 78073 3PR 24 AWG
ECOCABLE(R) MINI RU AWM 21460 80C 300V VW-1
C(RU) AWM I A/B FT1 80C 300V
CE ROHS (SEQ FOOTAGE)
* = Factory Code | |

B. Applicable Specifications

- | | | |
|----------------------|-------------------------------------|-----------------------------|
| 1) UL | AWM/STYLE 21460 | 80°C / 300 V _{RMS} |
| | VW-1 | |
| 2) CSA International | C(RU) AWM I A/B FT1 | 80°C / 300 V _{RMS} |
| 3) Other | Halogen-Free | |
| 4) CE: | EU Low Voltage Directive 2006/95/EC | |

C. Environmental Compliance

- | | |
|-------------------------------------|---|
| 1) CE: | EU Directive 2011/65/EU(RoHS2):
This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011. No Exemptions are required for RoHS Compliance on this item. Consult Alpha Wire's web site for RoHS C of C . |
| 2) REACH Regulation (EC 1907/2006): | This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration . |

D. Physical & Mechanical Properties

- | | |
|----------------------|--------------------|
| 1) Temperature Range | -40 to 80°C |
| 2) Bend Radius | 10X Cable Diameter |
| 3) Pull Tension | 22.4 Lbs, Maximum |

E. Electrical Properties

- | | |
|-----------------------------|---------------------------------|
| | (For Engineering purposes only) |
| 1) Voltage Rating | 300 V _{RMS} |
| 2) Mutual Capacitance | 18.9 pF/ft @1 kHz, Nominal |
| 3) Characteristic Impedance | 82 Ω |
| 4) Inductance | 0.17 μH/ft, Nominal |
| 5) Conductor DCR | 24.5 Ω/1000ft @20°C, Nominal |

F. Other

- | | |
|------------------------|-------------------------------------|
| 1) Packaging | Flange x Traverse x Barrel (inches) |
| a) 1000 FT | 12 x 6 x 3.5 Continuous length |
| b) 100 FT | 6.5 x 2 x 1.9 Continuous length |
| c) Bulk(Made-to-order) | |

[Spool dimensions may vary slightly]

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability. Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.