


- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
 3. TERMINAL NUMBERS FOR REF ONLY
 4. CONTACT RATING: CURRENT: 100mA
VOLTAGE: 30 VDC
 5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
 6. INSULATION RESISTANCE: 500VDC, 100M OHM, MIN.
 7. OPERATING FORCE: $250gf \pm 100$ GRAMS
 8. OPERATING TEMP.: -20°C to 70°C
 9. TRAVEL: $1.00 \pm 0.3\text{mm}$ LOCK
 $1.50 \pm 0.3\text{mm}$ FULL TRAVEL
 10. CONTACT RESISTANCE: 50 m OHM, MAX.
 11. ▲ DENOTES CRITICAL PARAMETER.
 12. 2002/95/EC (ROHS) COMPLIANT
 13. LED COLOR: WHITE



D	19601	DRAWING UPDATE	1/19/11	BGL	
					</



B	19100	revised to comply terminus	1C
A	18354	RELEASE FOR PRODUCTION	R/R
			TITLE LP4EE1RBATW

REV	PCR NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
SCALE 2 = 1				
DATE 12/18/2008				
DR BLR				
DWG B240013				
REV D				