

Coaxial

Power Splitter/Combiner

ZMSC-4-1

4 Way-0° 50Ω

0.1 to 200 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.250W max.

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

Features

- high isolation, 30dB typ.
- rugged, shielded case

Applications

- HF/VHF
- radio communication
- receivers/transmitters



CASE STYLE: N24


Connectors	Model	Price	Qty.
SMA	ZMSC-4-1	\$66.95	(1-9)
BRACKET (OPTION "B")		\$5.00	(1+)
BRACKET (OPTION "BR")		\$1.50	(1+)

Splitter Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 6 dB						PHASE UNBALANCE (Degrees)						AMPLITUDE UNBALANCE (dB)					
	L		M		U		L		M		U		L		M		U		L		M		U	
	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.	Max.	Max.	Max.	Max.	Max.	Max.	
f _l -f _u	33	20	30	20	27	20	0.4	0.6	0.5	0.75	0.7	1.0	4	6	8	0.15	0.20	0.25						

L = low range [f_L to 10 f_L] M = mid range [10 f_L to $f_U/2$] U = upper range [$f_U/2$ to f_U]

Outline Drawing






Typical Performance Data

Freq. (MHz)	Insertion Loss (dB)				Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR				
	S-1	S-2	S-3	S-4		1-2	2-3	3-4		S	1	2	3	4
0.10	6.17	6.17	6.17	6.16	0.01	28.93	32.05	29.34	0.07	1.27	1.31	1.31	1.32	1.32
0.50	6.20	6.20	6.20	6.20	0.00	29.03	43.97	29.35	0.05	1.24	1.18	1.18	1.19	1.19
1.00	6.19	6.19	6.19	6.18	0.01	28.87	45.99	29.14	0.05	1.25	1.17	1.17	1.17	1.17
10.00	6.20	6.21	6.21	6.21	0.01	29.26	46.44	29.47	0.06	1.27	1.15	1.15	1.15	1.15
31.00	6.29	6.29	6.29	6.29	0.01	29.41	45.20	29.56	0.04	1.28	1.14	1.14	1.14	1.14
52.00	6.34	6.34	6.34	6.35	0.01	29.05	43.18	29.13	0.05	1.28	1.13	1.13	1.13	1.13
80.00	6.35	6.35	6.36	6.36	0.02	28.55	41.17	28.52	0.07	1.26	1.11	1.10	1.10	1.11
100.00	6.40	6.40	6.43	6.43	0.02	28.45	40.30	28.37	0.06	1.24	1.09	1.09	1.09	1.09
118.00	6.40	6.41	6.43	6.44	0.04	28.68	39.86	28.52	0.07	1.21	1.08	1.08	1.07	1.07
130.00	6.40	6.40	6.44	6.44	0.05	29.03	39.76	28.83	0.09	1.19	1.07	1.07	1.06	1.07
154.00	6.45	6.45	6.50	6.51	0.06	30.28	40.30	30.13	0.10	1.14	1.07	1.07	1.06	1.06
176.00	6.49	6.48	6.55	6.57	0.09	32.10	41.55	32.45	0.19	1.09	1.09	1.09	1.08	1.07
184.00	6.50	6.49	6.57	6.59	0.10	32.76	42.38	33.67	0.19	1.08	1.10	1.10	1.09	1.08
192.00	6.51	6.51	6.59	6.62	0.11	33.28	43.49	35.26	0.22	1.07	1.11	1.11	1.10	1.09
200.00	6.52	6.51	6.60	6.63	0.12	33.46	44.99	37.10	0.25	1.06	1.12	1.12	1.11	1.10

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
1.50	1.13	1.00	.50	.155	2.345	.138	.987	2.50
38.10	28.70	25.40	12.70	3.94	59.56	3.51	25.07	63.50
K	L	M	N	P	Q	R	S	wt
.10	.32	.75	1.18	.31	.56	.81	.150	grams
2.54	8.13	19.05	29.97	7.87	14.22	20.57	3.81	45.0



electrical schematic

