



REVISONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
C		REVISED PER ECO-11-017736	30SEP2011	DD	RB
C1		REVISED PER ECO-14-013809	16SEP2014	DD	RB
D		REV PER ECO-16-011480	02AUG2016	JM	RB
E		REV PER ECO-16-014045	13SEP2016	JM	RB


1 DIMENSION TO BE MEASURED WHEN THE COVER IS CLOSED.
2 COLOR: BLACK




2035047-1




2035047-2




2035047-3




2035047-4







2035047-5




2035047-6




SECTION A - A




2035047-7




2035047-8



2035047-9



1-2035047-0



1-2035047-1

TE PART NUMBER	ASSY POSN	NOMINAL CONDUIT SIZE		NOMINAL DIMENSIONS			
		NC	NW	C	D	E	(K)
2035047-1	2	08	7.5	24.0	18.5	34.5	12.5
2035047-2	3	08	7.5	28.5	18.5	34.5	12.5
2035047-3	4	08	7.5	29.0	23.5	38.5	12.5
2035047-4	6	08	7.5	28.7	23.5	36.8	11.1
2035047-5	4	12	10	29.0	23.5	36.8	10.7
2035047-6	6	12	10	28.7	23.5	36.8	10.7
2035047-7	8	12	10	33.0	23.5	36.8	10.7
2035047-8	12	12	10	42.0	23.5	36.8	10.7
2035047-9	8	16	13	33.0	23.5	36.8	10.7
1-2035047-0	12	16	13	42.0	23.5	36.8	10.7
1-2035047-1	12	20	17	41.7	23.5	48.0	12.1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MARKEY CHK J. MARKEY APVD J. MARKEY	11APR2008 11APR2008 11APR2008
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		±0.6 ± ± ± ± ± ±	
MATERIAL NYLON 6/6		WEIGHT -	
		CUSTOMER DRAWING	
		SCALE 3:1	
		SHEET 1 OF 1	
		REV E	

TE Connectivity

BACKSHELL,
AMPSEAL16, 0 DEGREE EXIT

A100779C=2035047