





© COPYRIGHT 1975 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	DESCRIPTION	DATE	APPROVED
		A	REVISED M.S. 4570	10-75	DR
		B	REVISED AS 5336	5-78	M.S.
		B1	REVISED 6098 M.S.	6-79	
		C	REVISED PER ECN 8454 ZPL	5-83	
		D	REVISED PER ECN AD0188	5/11/84	R.f.
		D1	REV PER AD1111	2/18/86	
		D2	REVISED PER AD1276	4/18/86	CP
		E	085-8 PER ECN 0655-93	6-93	RAC
		F	REV. PER 0010-1154-95	11-95	PG.
		G	REV PER 0652-0070-99	4JUN99	MM
		H	REV PER EC 063C-233-01	08OCT01	MM
		H1	REVISED PER ECO-10-000445	09JAN10	AEG



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN M. M.		CONTRACT NO.		AMP INCORPORATED Harrisburg, Pa.	
TOLERANCES ON:		DR		NAME	
DECIMALS ± 0.127		CHK		HOUSING, HIGH-CURRENT CONNECTOR.	
ANGLES ± [0.05]		APPD		SIZE CODE IDENT NO DRAWING NO	
MATERIAL		APPD		C 00779 530521	
GLASS FILLED POLYESTER		DSGN APPD		SCALE 4:1	
COLOR- NATURAL (WHITE)		OTHER APPD		SHEET 1 OF 2	
FINISH					

© COPYRIGHT 1975 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS

REV	ZONE	LTR	DESCRIPTION	DATE	APPROVED
1			SEE SHEET 1 of 2		

PART NO.	NO POS.	$\pm .015$ A	$\pm .007$ B	C	D	$\pm .010$ $\pm .0254$ E	X	Y	Z	INCH M M TYP. — OBSOLETE
530521-1	2	1.660 [42.16]	1.226 [31.14]	.852 [21.64]	.712 [8.08]	.802 [20.37]	1	.312 [7.92]	.312 [7.42]	
530521-2	3	1.972 [50.09]	1.538 [39.06]	1.164 [29.56]	1.024 [26.00]	1.114 [28.29]	2		.624 [15.84]	OBSOLETE
530521-3	4	2.284 [58.01]	1.850 [46.99]	1.476 [37.49]	1.336 [33.93]	1.426 [36.22]	3		.936 [23.77]	
530521-4	5	2.596 [65.94]	2.162 [54.91]	1.788 [45.41]	1.648 [41.85]	1.738 [44.14]	4		1.248 [31.69]	OBSOLETE
530521-5	6	2.908 [73.86]	2.474 [62.54]	2.100 [53.34]	1.960 [49.74]	2.050 [52.07]	5		1.560 [39.62]	OBSOLETE ³
530521-6	8	3.532 [89.71]	3.098 [78.69]	2.724 [69.18]	2.584 [65.63]	2.674 [67.92]	7		2.184 [55.47]	
530521-7	9	3.844 [97.63]	3.410 [86.61]	3.036 [77.11]	2.896 [73.55]	2.986 [75.84]	8		2.496 [63.39]	
530521-8	10	4.156 [105.56]	3.722 [94.54]	3.348 [85.04]	3.208 [81.48]	3.298 [83.77]	9		2.808 [71.32]	OBSOLETE
530521-9	12	4.780 [121.41]	4.346 [110.39]	3.972 [100.89]	3.832 [97.33]	3.922 [99.62]	11	.312 [7.92]	3.432 [87.17]	

1 MEASURE ACROSS MOUNTING EARS. MAY GO TO .020 [0.51]
OVER NOMINAL AT TOP OF HOUSING.

2. VOID CORING OPTIONAL.

3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm$ ANGLES $\pm$		CONTRACT NO		PART NO	
MATERIAL		DR <i>Amble</i> 5-14-75 CHK <i>Amble</i> 5-14-75 APPD		NAME HOUSING, HIGH CURRENT CONNECTOR	
FINISH		APPD <i>R. Shorman</i> 5/14/75 DSGN APPD		SIZE CODE IDENT NO DRAWING NO C 00779 530521	
		OTHER APPD		SCALE SHEET 2 OF 2	