

Duplex Multimode 50/125 Fiber Patch Cable (SC/ST), 2M (6-ft.)

MODEL NUMBER: **N504-02M**



Highlights

- Premium PVC 50/125 μ m multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

Package Includes

- 2-meter (6ft-7ft) duplex MMF cable ST/SC 50/125 fiber

Description

Tripp Lite's 2-meter (6ft-7ft) multimode duplex fiber optic SC/ST patch cable is manufactured from 50/125 zipcord fiber. The cable has ST to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 50/125 duplex (zipcord) fiber
- PVC jacket
- Length: 2-meters(6ft-7ft) - Connectors: 2 ST to 2 SC connectors
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	50/125 - OM2
Intended Application	Computer Networking (Fiber)

Cable Type	MULTIMODE 50/125 FIBER OPTIC
Model Type	SC/ST
Network Speed	1Gbps
INPUT	
Cable Length (m)	2
UPC ASSIGNMENT	
Unit Carton UPC#	037332134806
PHYSICAL	
Color	Orange
Style	Fiber Optic
CONNECTIONS	
Connector A	SC
Connector B	ST
Number of Connectors	4
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.