

1-1478672-7 Product Details

[Share](#) [Print](#) [Email](#)


1-1478672-7

TE Internal Number: 1-1478672-7

 [Active](#)

Snap Action Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Switch Style = Miniature
- Actuator Style = Roller, Simulated
- Termination Type = .187 x .020 Quick Connect Terminals, Solder
- Single Pole - Normally Open Configuration (Pole-Throw)
- Contact Rating = 0.1A

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Micro Switch NO Solder Terminal](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Actuator Style = Roller, Simulated
- Termination Type = .187 x .020 Quick Connect Terminals, Solder
- Configuration (Pole-Throw) = Single Pole - Normally Open

Mechanical Attachment:

- Operating Force (g [oz]) = 55 [1.940]

Electrical Characteristics:

- Contact Rating = 0.1A

Body Features:

- Switch Style = Miniature
- Releasing Force (g [oz]) = 15 [0.529]
- Pre Travel (mm [in]) = 2.80 [0.110]
- Operating Position (mm [in]) = 18.70 [0.736]
- Over Travel (mm [in]) = 2.40 [0.094]
- Movement Differential (mm [in]) = 1.10 [0.043]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Tyco Electronics

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

