




ADTSA644LV
ADTSA=RIGHT ANGLE TYPE
TACTILE SWITCH

PROD. SIZE
6=6x6mm

DIMENSION H: 44=.242 [6.15]
48=.242 [6.15]

SOLDERING:
V=LEAD FREE
N=BROWN, 160gf
R=RED, 260gf
S=SALMON, 320gf

DATE	SYM	REVISION RECORD	DWN.	CK.

PART NO.	DIM. A	DIM. B
ADTSA644*V	.095	.063
ADTSA648*V	.110	.079



DESCRIPTION: MECHANICAL CONTACT SWITCH
SPECIFICATIONS:

STORAGE TEMP. RANGE:-30°C TO +80°C
OPERATING TEMPERATURE RANGE: -25°C to +70°C
RATING: 50mA AT 12VDC
CONTACT RESISTANCE: 100mohm MAX.
INSULATION RESISTANCE: 100Mohm MIN. 500VDC.
DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE
ELECTRICAL LIFE: 100,000 CYCLES FOR 320gf,260gf
ELECTRICAL LIFE: 200,000 CYCLES FOR 160gf
SHOCK RESISTANCE: 50G PER METHOD 213B,
MIL-STD-202F
VIBRATION RESISTANCE: PASSES METHOD 201A,
MIL-STD-202F
CONTACT ARRANGEMENT: 1 POLE, 1 THROW.


MATERIALS:

COVER: STEEL, TIN PLATED
CONTACT DISC: PHOSPHOR BRONZE WITH SILVER CLADDING
TERMINAL: BRASS WITH SILVER PLATING
BASE: UL 94V-0 NYLON THERMOPLASTIC COLOR: BLACK
STEM: UL 94V-0 NYLON THERMOPLASTIC
SOLDERING:
IR REFLOW: 260°C MAX.
HAND SOLDERING: 350°C MAX. FOR 5 SECONDS MAX.
(30 WATT IRON MAX.)

RoHS COMPLIANT
LEAD FREE PROCESS COMPATIBLE



CIRCUIT DIAGRAM



APTEM CONFIDENTIAL
THIS DOCUMENT CONTAINS INFORMATION WHICH IS THE EXCLUSIVE PROPERTY OF APEM COMPONENTS, INC. DISTRIBUTION, REPRODUCTION OR USE BY OTHERS IS NOT PERMITTED WITHOUT THE EXPRESS WRITTEN CONSENT OF APEM COMPONENTS, INC.

TOLERANCES (EXCEPT AS NOTED)		APTEM	
DECIMAL ± .008	INCH (MM)	SCALE	DRAWN CJD
FRACTIONAL ± —	ANGULAR ± —	TITLE TACTILE SWITCH R/A	DATE 06/22/05
		DRAWING NUMBER ADTSA64**V	REV —