






2 HOLES FLANGE JACK RECEPTACLE
R128.464.231
WITH CYLINDRICAL CONTACT

 Series : **BMA**

PANEL CUT OUT


	mm	
	Maxi	mini
A	4.14	4.1
B	2.8	2.6
C	12.3	12.2



All dimensions are in mm.

COMPONENTS	MATERIALS	PLATING
BODY	STAINLESS STEEL	PASSIVATED . μm
CENTRE CONTACT	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL 2 μm
OUTER CONTACT	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL 2 μm
INSULATOR	PTFE	
GASKET	-	
OTHERS PARTS	STAINLESS STEEL	PASSIVATED . μm
-	-	-
-	-	-


RADIALl®

Edition : 9926 C

Design changes may be in order to improve the product.

2 HOLES FLANGE JACK RECEPTACLE**R128.464.231****WITH CYLINDRICAL CONTACT**Series : **BMA****ELECTRICAL CHARACTERISTICS**

Impedance		50 Ω
Frequency		0-22 GHz
VSWR	1.25* +	0.000 x F(GHz) Maxi
Insertion loss		0.07 $\sqrt{F(GHz)}$ dB Maxi
RF leakage	- (	NA - F(GHz)) dB mini
Voltage rating		500 Veff Maxi
Dielectric withstanding voltage		1500 Veff mini
Insulation resistance		5000 M Ω mini

SPECIFICATION**ENVIRONMENTAL**

Operating temperature	-65/+125 °C
Hermetic seal	NA Atm.cm3/s
Leakage – pressurised only	NA Mpa

MECHANICAL CHARACTERISTICS

Centre contact retention	
Axial force – Mating end	27 N mini
Axial force – Opposite end	27 N mini
Torque	NA N.cm mini
Recommended torque	
Mating	NA N.cm
Panel nut	NA N.cm
Mating life	1000 Cycles mini
Weight	0.000 g

OTHERS CHARACTERISTICS

Assembly instruction NA

Others :
* de 0 -10 Ghz**RADIALL®**

Edition : 9926 C

Design changes may be in order to improve the product.