

### GLOBAL PERFORMANCE SWITCHERS

#### FEATURES:

- **Industry's smallest 15 W medically approved switcher**
- **Compact size (3.00" x 2.10" x 0.92")**
- **Wide-range ac input: 90-264 Vac**
- **Less than 75  $\mu$ A leakage current @ 120 Vac**
- **Approved to UL2601-1, EN60601-1**
- **EMI to FCC, CISPR 11 Class B**
- **Overvoltage protection standard**
- **RoHS compliant models available (G suffix)**
- **CE marked to LVD**



#### SPECIFICATIONS

Ac Input 90-264 Vac, 47-63 Hz single phase. Class I or class II grounding.	Temperature Coefficient 0.03% / °C typical.		
Input Current Maximum input current at 90 Vac, 60 Hz with full rated output load not to exceed 0.6 A.	EMI/EM Compliance All models include built-in EMI filtering to meet the following EMC requirements of IEC601-1-2.		
Input Protection Internal ac fuse provided on all units. Designed to blow only if a catastrophic failure occurs in the unit -- Fuse does not blow on unsustained overload or short circuit.	Performance Requirement   EMC Standard   Typical Margin		
Inrush Current Inrush is limited by internal thermistors. The inrush at 240 Vac, averaged over the first ac half-cycle under cold start conditions will not exceed 37 A.	Conducted Emissions   EN55011, Class B; FCC Class B   2 dB Class II Gnd 6 dB Class I Gnd		
Efficiency 69-85% depending on model.	Surge Discharge   EN61000-4-2, Level 3   2 kV		
Overload Protection Fully protected against short circuit and output overload. Short circuit protection is cycling type power limit. Factory set to begin power limiting at 23 W.	RF Field Susceptibility   EN61000-4-3, Level 3   2 V		
Overvoltage Protection Built in OVP on all models. Approximately 120-140% of output voltage.	Fast Transients/Bursts   EN61000-4-4, Level 3   500 V		
Output Noise 0.5% rms, 1% Pk-Pk, 20 MHz Bandwidth, differential mode. Measured with noise probe directly across output terminals of the power supply.	Surge Susceptibility   EN61000-4-5, Level 3   500 V		
Transient Response Main Output - 500 $\mu$ s max. response time for return to within 0.5% of final value for a 50% load step change, $\Delta i / \Delta t < 0.2 \text{ A}/\mu\text{s}$ . Maximum voltage deviation is 3.5%.	Conducted RF Susceptibility   EN61000-4-6   25%		
Hold-up Time 10 ms minimum from loss of ac input voltage at full load, nominal line (120 Vac).	Voltage Sags & Surges   EN61000-4-11   5%		
Medical Safety Approvals All models are Certified to be in compliance with the applicable requirements of UL2601-1, IEC60601-1, CSA-C22.2 No. 601-1, EN60601-1.			
Leakage Current The maximum leakage current for GSM15 series will be as follows;			
132Vac/60Hz UL2601-1 test method			
	GND	Connection Normal	Single Fault
	Class I	75 $\mu$ A	105 $\mu$ A
	Class II	39 $\mu$ A	54 $\mu$ A
264Vac/50Hz IEC60601-1 test method			
	GND	Connection Normal	Single Fault
	Class I	128 $\mu$ A	180 $\mu$ A
	Class II	66 $\mu$ A	94 $\mu$ A

Medical Model	Voltage Output	Min.	Normal (A)	Peak (B)	Initial Set Point	OVP Setpoint	Total Regulation	Ripple and Noise
GSM15-5	5.1 V	0 A	2.35 A	3 A	2.5%	7.2 V	2%	1%
GSM15-12	12V	0 A	1.25 A	1.5 A	2.5%	16 V	2%	1%
GSM15-15	15 V	0 A	1.0 A	1.2 A	2.5%	21 V	2%	1%
GSM15-24	24 V	0 A	0.625 A	0.75 A	2.5%	32 V	2%	1%
GSM15-28	28 V	0 A	0.54 A	0.64 A	2.5%	280 V	2%	1%

Notes:

- A. Rating with unrestricted convection cooling.
- B. Peak Power for 60 sec. 10% duty cycle or continuous rating with 150 LFM of airflow.
- C. Output voltages preset at factory, not user adjustable.
- D. Add "G" suffix to model number for RoHS compliant model.

## GSM15 MECHANICAL SPECIFICATIONS

INPUT: J1 AMP P/N 640456-4

PIN 1) AC LINE

PIN 2) N/C

PIN 3) N/C

PIN 4) AC NEUTRAL

GND: 0.098 DIA. THRU HOLE

OUTPUT: J2 AMP P/N 640456-4

PIN 1) COMMON Return

PIN 2) COMMON Return


PIN 3) OUTPUT #1 + Vout

PIN 4) OUTPUT#1 +Vout

MATING CONNECTOR AMP P/N

MTA – 100 Receptacle

NOTE: 3A MAXIMUM RECOMMENDED CURRENT PER CONNECTOR PIN



Overall Dimensions:  
 3.00 x 2.10 x .92 inches  
 76.20mm x 53.34mm x 23.37mm  
 Weight: 0.25 LBS. [.113 kg]  
 MAX.

ENVIRONMENTAL SPECIFICATIONS	OPERATING	NON-OPERATING
Temperature (A)	0 to 50°C	-40 to +85°C
Humidity (A)	0 to 95% RH	0 to 95% RH
Shock (B)	20 g <sub>pk</sub>	40 g <sub>pk</sub>
Altitude	-500 to 10,000 ft	-500 to 40,000 ft
Vibration (C)	1.5 g <sub>rms</sub> , 0.003 g <sup>2</sup> /Hz	5 g <sub>rms</sub> , 0.026 g <sup>2</sup> /Hz

- A. Units should be allowed to warm up/operate under non-condensing conditions before application of power.
- B. Shock testing—half-sinusoidal, 10 ± 3 ms duration, ± direction, 3 orthogonal axes, total 6 shocks.
- C. Random vibration—10 to 2000Hz, 6dB/octave roll-off from 350 to 2000Hz, 3 orthogonal axes. Tested for 10 min./axis operating and 1 hr./axis non-operating.

SL Power Electronics Corp., 6050 King Drive, Bldg. A, Ventura, CA 93003, USA. Phone:(805) 486 4565 Fax:(805) 487 8911 www.slpower.com Rev. 1/07.

Data Sheet © 2007 SL Power Electronics Corp. The information and specifications contained in this data sheet are believed to be correct at time of publication. However, Condor accepts no responsibility for consequences arising from reproduction errors or inaccuracies. Specifications are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SL Power](#):

[GSM15-5](#) [GSM15-24](#) [GSM15-15](#) [GSM15-12](#) [GSM15-12G](#) [GSM15-5G](#) [GSM15-15G](#) [GSM15-24G](#)