

REV.	DESCRIPTION	DATE	APPROVED
N	Edit MFG tables per ECO-1125	04/08/22	R. P.
P	Remove extrusion profile table per ECO-1136	05/27/22	R. P.
R	Remove extrusion length 937 per ECO-1313	02/10/25	D. A.
T	Add angle tolerance per ECO-1321	03/27/25	D. A.
U	Updated angle tolerance per ECO-1339	07/18/25	D. A.

ORDERING INFORMATION:

9XX-XXX

SERIES LENGTH

INCHES, MULTIPLES OF .005"

.030" = 030


.100" = 100

1.250" = 1.250

WHOLE MILLIMETERS

2mm = 2MM

5mm = 5MM



SERIES	"H" DIMENSION	I. D.	O.D.	Wall Thick (REF)
901	.030-1.250 (.76-31.8)	0.028 (0.71)	0.085 (2.2)	0.029 (0.72)
902	.030-1.250 (.76-31.8)	0.032 (0.81)	0.125 (3.2)	0.047 (1.18)
903	.030-1.250 (.76-31.8)	0.047 (1.2)	0.156 (4.0)	0.055 (1.38)
904	.030-1.250 (.76-31.8)	0.063 (1.6)	0.187 (4.7)	0.062 (1.57)
905	.030-1.250 (.76-31.8)	0.147 (3.7)	0.250 (6.4)	0.052 (1.31)
906	.030-1.250 (.76-31.8)	0.085 (2.2)	0.148 (3.8)	0.032 (0.80)
907	.030-1.250 (.76-31.8)	0.105 (2.7)	0.167 (4.2)	0.031 (0.79)
908	.030-1.250 (.76-31.8)	0.125 (3.2)	0.187 (4.7)	0.031 (0.79)
911	.030-1.250 (.76-31.8)	0.125 (3.2)	0.250 (6.4)	0.063 (1.59)
912	.030-1.250 (.76-31.8)	0.171 (4.3)	0.250 (6.4)	0.040 (1.00)
913	.030-1.250 (.76-31.8)	0.091 (2.3)	0.187 (4.7)	0.048 (1.22)
938	.030-1.250 (.76-31.8)	0.032 (0.8)	0.085 (2.2)	0.027 (0.67)
940	.030-1.250 (.76-31.8)	0.063 (1.6)	0.156 (4.0)	0.047 (1.18)

CUSTOMER USE DRAWING

3. TOLERANCE "H" DIMENSION:

0.030 - 0.500 (1.0 - 12.7mm) ± 0.005 (0.1mm)

0.505 - 0.750 (12.8 - 19.1mm) ± 0.008 (0.2mm)

0.755 - 1.250 (19.2 - 31.8mm) ± 0.015 (0.4mm)

2. MATERIAL: NYLON 6, NYCOA 589, CLEAR WITH 1% AVIENT AB0SAF WHITE NYLON CONCENTRATE. BIVAR MATERIAL CODE 01-CR-WE.

1. GENERAL SPECIFICATIONS: BIVAR EXTRUDED PRODUCT SPECIFICATION BV00-E103.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	TITLE: NYLON TUBE SPACERS	
.XX ± .01			
.XXX ± .005			
DESIGNED: M. CHEN	DATE: 1/3/2003	PART NO: 9XX-XXX	
REVISION: K. BARON	DATE: 7/18/2025	REVISION: U	
		SHEET SIZE	A
		CAGE CODE: 32559	
CHECKED: D. ASHBY	DATE: 7/18/2025	SCALE: 2:1	
		SHEET # 1 OF 1	
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			