


Data Sheet



Type Number 6237
Designation IEC ---
System Li-Manganese dioxide / Organic Electrolyte

UL Recognition MH 13654 (N)
Nominal Voltage 3 V
Typical Capacity C 1350 mAh
 Load 1.0 kOhm, at 20°C down to 2.0 V

Weight (approx.) 15 g
Volume 5,6 ccm
Coding Date of Manufacturing Month / Year

Temperature Ranges	min	max.
Storage	-55°C	75 °C
Discharge	-30°C	75°C

Dimensions	min	max.
Diameter (A)	14,45	14,75
Height (B)	33,1	33,5
Shoulder Diameter[L].....	7	
Shoulder Height [M].....	0,6	

Segment Electronic

Main Applications Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0 V
Continuous 24h/d,7d/w	1000 Ω	Time: Capacity [mAh]: Energy [mWh]:	500 h 1350 3600

All Data contained herein is for single cells

For battery applications, performance data may vary from single cell data, depending on specific battery configuration

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst
 Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Subject to change without prior notice!
 Date of issue: 2012-10-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[6237101301](#)