

BCR5AS

MEDIUM POWER USE

NON-INSULATED TYPE, PLANAR PASSIVATION TYPE

Refer to the page 6 as to the product guaranteed maximum junction temperature 150°C


BCR5AS



- I_T (RMS) 5A
- V_{DRM} 600V
- I_{FGT} I , I_{RGT} I , I_{RGT} III 30mA

OUTLINE DRAWING

Dimensions
in mm



APPLICATION

Hybrid IC, solid state relay, switching mode power supply, light dimmer, electric fan, electric blankets, control of household equipment such as washing machine, other general purpose control applications

MAXIMUM RATINGS

Symbol	Parameter	Voltage class	Unit
		12	
V_{DRM}	Repetitive peak off-state voltage *1	600	V
V_{DSM}	Non-repetitive peak off-state voltage *1	720	V

Symbol	Parameter	Conditions	Ratings	Unit
I_T (RMS)	RMS on-state current	Commercial frequency, sine full wave 360° conduction, $T_c=103^\circ\text{C}^{*3}$	5	A
I_{TSM}	Surge on-state current	60Hz sinewave 1 full cycle, peak value, non-repetitive	50	A
I^2_t	I^2_t for fusing	Value corresponding to 1 cycle of half wave 60Hz, surge on-state current	10.4	A ² s
PGM	Peak gate power dissipation		3	W
PG (AV)	Average gate power dissipation		0.3	W
VGM	Peak gate voltage		10	V
IGM	Peak gate current		2	A
T_j	Junction temperature		-40 ~ +125	°C
T_{stg}	Storage temperature		-40 ~ +125	°C
—	Weight	Typical value	0.26	g

*1. Gate open.

BCR5AS

Refer to the page 6 as to the product guaranteed
maximum junction temperature 150°C

MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE

ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Test conditions	Limits			Unit
			Min.	Typ.	Max.	
IdRM	Repetitive peak off-state current	T _J =125°C, V _{DRM} applied	—	—	2.0	mA
V _{TM}	On-state voltage	T _C =25°C, I _{TM} =7A, Instantaneous measurement	—	—	1.8	V
V _{FGT} I	Gate trigger voltage *2	T _J =25°C, V _D =6V, R _L =6Ω, R _G =330Ω	—	—	1.5	V
V _{RGT} I			—	—	1.5	V
V _{RGT} III			—	—	1.5	V
I _{FGT} I	Gate trigger current *2	T _J =25°C, V _D =6V, R _L =6Ω, R _G =330Ω	—	—	30	mA
I _{RGT} I			—	—	30	mA
I _{RGT} III			—	—	30	mA
V _{GD}	Gate non-trigger voltage	T _J =125°C, V _D =1/2V _{DRM}	0.2	—	—	V
R _{th} (j-c)	Thermal resistance	Junction to case *3	—	—	3.0	°C/W
(dv/dt) _c	Critical-rate of rise of off-state commutating voltage *4	T _J =125°C	5	—	—	V/μs



*2. Measurement using the gate trigger characteristics measurement circuit.

*3. Case temperature is measured on the T₂ terminal.

*4. Test conditions of the critical-rate of rise of off-state commutating voltage is shown in the table below.

Test conditions	Commutating voltage and current waveforms (inductive load)
1. Junction temperature T _J =125°C 2. Rate of decay of on-state commutating current (di/dt) _c =-2.5A/ms 3. Peak off-state voltage V _D =400V	

PERFORMANCE CURVES




BCR5AS


Refer to the page 6 as to the product guaranteed maximum junction temperature 150°C

MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE


**GATE CHARACTERISTICS
(I, II AND III)**




**GATE TRIGGER CURRENT VS.
JUNCTION TEMPERATURE**




**GATE TRIGGER VOLTAGE VS.
JUNCTION TEMPERATURE**




**MAXIMUM TRANSIENT THERMAL
IMPEDANCE CHARACTERISTICS
(JUNCTION TO CASE)**



**MAXIMUM ON-STATE POWER
DISSIPATION**









**ALLOWABLE CASE TEMPERATURE
VS. RMS ON-STATE CURRENT**



BCR5AS

Refer to the page 6 as to the product guaranteed maximum junction temperature 150°C




MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE




BCR5AS

Refer to the page 6 as to the product guaranteed maximum junction temperature 150°C

MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE



GATE TRIGGER CHARACTERISTICS TEST CIRCUITS



BCR5AS

The product guaranteed maximum junction temperature 150°C (See warning.)

MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE


BCR5AS



- I_T (RMS) 5A
- V_{DRM} 600V
- I_{FGT} I , I_{RGT} I , I_{RGT} III 30mA

OUTLINE DRAWING

Dimensions
in mm



APPLICATION

Hybrid IC, solid state relay, switching mode power supply, light dimmer, electric fan, electric blankets, control of household equipment such as washing machine, other general purpose control applications

(Warning)

1. Refer to the recommended circuit values around the triac before using.
2. Be sure to exchange the specification before using. If not exchanged, general triacs will be supplied.

MAXIMUM RATINGS

Symbol	Parameter	Voltage class	Unit
		12	
V_{DRM}	Repetitive peak off-state voltage *1	600	V
V_{DSM}	Non-repetitive peak off-state voltage *1	720	V

Symbol	Parameter	Conditions	Ratings	Unit
I_T (RMS)	RMS on-state current	Commercial frequency, sine full wave 360° conduction, $T_c=128^\circ\text{C}^{*3}$	5	A
I_{TSM}	Surge on-state current	60Hz sinewave 1 full cycle, peak value, non-repetitive	50	A
I^2_t	I^2_t for fusing	Value corresponding to 1 cycle of half wave 60Hz, surge on-state current	10.4	A ² s
PGM	Peak gate power dissipation		3	W
PG (AV)	Average gate power dissipation		0.3	W
VGM	Peak gate voltage		10	V
IGM	Peak gate current		2	A
T_j	Junction temperature		-40 ~ +150	°C
T_{stg}	Storage temperature		-40 ~ +150	°C
—	Weight	Typical value	0.26	g

*1. Gate open.

BCR5AS

The product guaranteed maximum junction temperature 150°C (See warning.)

MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE

ELECTRICAL CHARACTERISTICS



Symbol	Parameter	Test conditions	Limits			Unit
			Min.	Typ.	Max.	
I_{DRM}	Repetitive peak off-state current	$T_J=150^{\circ}\text{C}$, V_{DRM} applied	—	—	2.0	mA
V_{TM}	On-state voltage	$T_c=25^{\circ}\text{C}$, $I_{TM}=7\text{A}$, Instantaneous measurement	—	—	1.8	V
$V_{FGT\text{ I}}$	Gate trigger voltage *2	$T_J=25^{\circ}\text{C}$, $V_D=6\text{V}$, $R_L=6\Omega$, $R_G=330\Omega$	—	—	1.5	V
$V_{RGT\text{ I}}$			—	—	1.5	V
$V_{RGT\text{ III}}$			—	—	1.5	V
$I_{FGT\text{ I}}$	Gate trigger current *2	$T_J=25^{\circ}\text{C}$, $V_D=6\text{V}$, $R_L=6\Omega$, $R_G=330\Omega$	—	—	30	mA
$I_{RGT\text{ I}}$			—	—	30	mA
$I_{RGT\text{ III}}$			—	—	30	mA
V_{GD}	Gate non-trigger voltage	$T_J=125^{\circ}\text{C}/150^{\circ}\text{C}$, $V_D=1/2V_{DRM}$	0.2/0.1	—	—	V
$R_{th(j-c)}$	Thermal resistance	Junction to case *3	—	—	3.0	$^{\circ}\text{C}/\text{W}$
$(dv/dt)_c$	Critical-rate of rise of off-state commutating voltage *4	$T_J=125^{\circ}\text{C}/150^{\circ}\text{C}$	5/1	—	—	$\text{V}/\mu\text{s}$

*2. Measurement using the gate trigger characteristics measurement circuit.

*3. Case temperature is measured on the T2 terminal.

*4. Test conditions of the critical-rate of rise of off-state commutating voltage is shown in the table below.

Test conditions	Commutating voltage and current waveforms (inductive load)
1. Junction temperature $T_J=125^{\circ}\text{C}/150^{\circ}\text{C}$ 2. Rate of decay of on-state commutating current $(di/dt)_c=-2.5\text{A/ms}$ 3. Peak off-state voltage $V_D=400\text{V}$	


PERFORMANCE CURVES

BCR5AS


The product guaranteed maximum junction temperature 150°C (See warning.)

MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE


**GATE CHARACTERISTICS
(I, II AND III)**




**GATE TRIGGER CURRENT VS.
JUNCTION TEMPERATURE**




**GATE TRIGGER VOLTAGE VS.
JUNCTION TEMPERATURE**




**MAXIMUM TRANSIENT THERMAL
IMPEDANCE CHARACTERISTICS
(JUNCTION TO CASE)**



**MAXIMUM ON-STATE POWER
DISSIPATION**









**ALLOWABLE CASE TEMPERATURE
VS. RMS ON-STATE CURRENT**



BCR5AS

The product guaranteed maximum junction temperature 150°C (See warning.)






MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE



BCR5AS

The product guaranteed maximum junction temperature 150°C (See warning.)



MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE



BCR5AS

The product guaranteed maximum junction
temperature 150°C (See warning.)

MEDIUM POWER USE
NON-INSULATED TYPE, PLANAR PASSIVATION TYPE

GATE TRIGGER CHARACTERISTICS TEST CIRCUITS**RECOMMENDED CIRCUIT VALUES
AROUND THE TRIAC**