





REV.	DATE	DESCRIPTION
NC	06/23/98	INITIAL RELEASE
A	02/24/03	UPDATE DRAWING FORMAT



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .100"

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8					DRAWN	G.R.S.	07/20/05							
7					CHECKED			PART DESCRIPTION BNC CRIMP PLUG (FOR RG-214 CABLE)						
6					ISSUED									
5					SHEET	1 OF 1		PART NO. 112589						
4	FERRULE	BRASS	NICKEL		1									
3	CONTACT PIN	BRASS	GOLD		1			DWG. NO. 112589.DWG						
2	INSULATOR	TEFLON	NATURAL		1									
1	SHELL/BODY	BRASS	NICKEL	1			REV. A		SIZE A		SCALE NA			
DESCRIPTION		MATERIAL	FINISH	QTY	CAD FILE C:/112/112589.DWG									