



Ceramic Disc Capacitors Class 1, 100 V (DC) Narrow Tolerance

FEATURES

- Low losses
- High stability
- High capacitance in small size
- Kinked (preferred) or straight leads.
- Lead (Pb)-free available.



APPLICATIONS

- Bypassing
- Coupling
- Resonant circuit.

DESIGN

The capacitors consist of a ceramic disc both sides of which are silver-plated. Connection leads are made of tinned copper having a diameter of 0.6 mm.

The capacitors have inward kinked leads with a spacing of 5 mm (0.200") and a lead length from 4 to 30 mm. Encapsulation is made of phenolic resin.



Capacitors with 5 mm (0.20") lead spacing.

CAPACITANCE RANGE:

Class 1, at 1 MHz, 1.2 V (RMS); 1.5 to 560 pF
1 kHz, $1 \pm 0.2V$ (RMS) for capacitance values higher than 1000 pF.

TEMPERATURE COEFFICIENTS:

Class 1 NP0; P100; N150; N750; N1500

RATED DC VOLTAGE:

100 V

SECTIONAL SPECIFICATIONS:

Class 1 IEC 60 384-8,
EIA 198

DIELECTRIC STRENGTH:

250 % of rated voltage

CLIMATIC CATEGORY:

Class 1 55/125/56

INSULATION RESISTANCE AT 100V (DC):

$\geq 10\,000\text{ M}\Omega$

OPERATING TEMPERATURE RANGE:

Class 1 - 55 to + 125 °C

TOLERANCE ON CAPACITANCE:

$\pm 0.25\text{ pF}$; $\pm 0.5\text{ pF}$; $\pm 2\%$

MARKING

Marking indicates capacitance value and tolerance in accordance with "EIA 198".

DISSIPATION FACTOR:

Class 1, $C \leq 30\text{ pF}$; $\leq 20 \times (10/C + 0.7) \times 10^{-4}$ maximum

Class 1, $C > 30\text{ pF}$; $\leq 20 \times 10^{-4}$

The capacitors meet the essential requirements of "EIA 198". Unless stated otherwise all electrical values apply at an ambient temperature of $25 \pm 3\text{ °C}$, at normal atmospheric conditions

LV 100 V Narrow Tolerance


Vishay BCcomponents

Ceramic Disc Capacitors
Class 1, 100 V (DC) Narrow Tolerance




TEMPERATURE COEFFICIENT IN ACCORDANCE WITH "RS198"

C = 0.0	0 = - 1	G = ± 30
M = 1.0	1 = - 10	H = ± 60
P = 1.5	2 = - 100	J = ± 120
R = 2.2	3 = - 1000	K = ± 250
S = 3.3	5 = + 1	L = ± 500
T = 4.7	6 = + 10	M = ± 1000
U = 7.5	7 = + 100	N = ± 2500
-	8 = + 1000	-



Capacitance change as a function of temperature



Capacitance change as a function of temperature



LV 100 V Narrow Tolerance

Ceramic Disc Capacitors
Class 1, 100 V (DC) Narrow Tolerance

Vishay BCcomponents

ORDERING INFORMATION, CLASS 1, 100 V (DC), KINKED										
C (pF)	TOL. (%)	D _{max} (mm)	LEAD SPACING ⁽²⁾ F (mm)	SH ⁽³⁾ (mm)	CLEAR TEXT CODE	PACKAGING CODE 8 th AND 9 th DIGIT ⁽⁴⁾			CATALOG NUMBER ⁽⁵⁾ 3 rd DIGIT: 5 = STANDARD 8 = RoHS COMPLIANT	
					13 th DIGIT: T = REEL; U = AMMO; 3 = BULK 16 th DIGIT: R = RoHS COMPLIANT	REEL	AMMO	BULK		
CLASS 1 P100										
1.5	± 0.25 pF	5.0	5.0	4.0	D159C20M7GH6.J5.	06	08	10	22.2 596 ..144	
2.2					D229C20M7GH6.J5.				22.2 596 ..244	
3.3					D339C20M7GH6.J5.				22.2 596 ..344	
4.7					D479C20M7GH6.J5.				22.2 596 ..444	
6.8	± 2 %	6.5			D689C20M7GH6.J5.				22.2 596 ..644	
10					D100G25M7GH6.J5.				22.2 596 ..004	
15					D150G29M7GH6.J5.				22.2 596 ..104	
22					D220G33M7GH6.J5.				22.2 596 ..204	
33					D330G39M7GH6.J5.				22.2 596 ..304	
47					D470G43M7GH6.J5.				22.2 596 ..404	
CLASS 1 NP0										
1.5	± 0.25 pF	5.0	5.0	4.0	D159C20C0KH6.J5.	06	08	10	22.2 506 ..144	
1.8					D189C20C0KH6.J5.				22.2 506 ..194	
2.2					D229C20C0JH6.J5.				22.2 506 ..244	
3.3					D339C20C0JH6.J5.				22.2 506 ..344	
4.7					D479C20C0HH6.J5.				22.2 506 ..444	
6.8	D689C20C0HH6.J5.				22.2 506 ..644					
10	± 2 %				6.5				D100G20C0GH6.J5.	22.2 506 ..004
15									D150G20C0GH6.J5.	22.2 506 ..104
22									D220G20C0GH6.J5.	22.2 506 ..204
33									D330G20C0GH6.J5.	22.2 506 ..304
47		D470G25C0GH6.J5.							22.2 506 ..404	
68		D680G25C0GH6.J5.							22.2 506 ..604	
100		D101G29C0GH6.J5.							22.2 506 ..014	
150		D151G33C0GH6.J5.							22.2 506 ..114	
220		D221G43C0GH6.J5.							22.2 506 ..214	
CLASS 1 N150										
3.9	± 0.25 pF	5.0	5.0	4.0	D399C20P2JH6.J5.	06	08	10	22.2 516 ..394	
4.7					D479C20P2HH6.J5.				22.2516 ..444	
6.8					D689C20P2HH6.J5.				22.2 516 ..644	
10	± 2 %				6.5				D100G20P2GH6.J5.	22.2 516 ..004
15									D150G20P2GH6.J5.	22.2 516 ..104
22									D220G20P2GH6.J5.	22.2 516 ..204
33									D330G20P2GH6.J5.	22.2 516 ..304
47									D470G25P2GH6.J5.	22.2 516 ..404
68		D680G25P2GH6.J5.							22.2 516 ..604	
100	7.5	D101G29P2GH6.J5.			22.2 516 ..014					
150	10.0	D151G39P2GH6.J5.			22.2 516 ..114					
220	11.0	D221G43P2GH6.J5.			22.2 516 ..214					

LV 100 V Narrow Tolerance

Vishay BCcomponents

Ceramic Disc Capacitors
Class 1, 100 V (DC) Narrow Tolerance



ORDERING INFORMATION, CLASS 1, 100 V (DC), KINKED														
C (pF)	TOL. (%)	D _{max} (mm)	LEAD SPACING ⁽²⁾ F (mm)	SH ⁽³⁾ (mm)	CLEAR TEXT CODE	PACKAGING CODE 8 th AND 9 th DIGIT ⁽⁴⁾			CATALOG NUMBER ⁽⁵⁾ 3 rd DIGIT: 5 = STANDARD 8 = RoHS COMPLIANT					
					13 th DIGIT: T = REEL; U = AMMO; 3 = BULK 16 th DIGIT: R = RoHS COMPLIANT	REEL	AMMO	BULK						
CLASS 1 N750														
6.8	± 0.25 pF	5.0	5.0	4.0	D689C20U2JH6.J5.	06	08	10	22.2 556 ..644					
10	± 2 %				D100G20U2JH6.J5.				22.2 556 ..004					
15					D150G20U2JH6.J5.				22.2 556 ..104					
22					D220G20U2JH6.J5.				22.2 556 ..204					
33					D330G20U2JH6.J5.				22.2 556 ..304					
47					D470G20U2JH6.J5.				22.2 556 ..404					
68		6.5			D680G25U2JH6.J5.				22.2 556 ..604					
100		7.5			D101G29U2JH6.J5.				22.2 556 ..014					
150		8.5			D151G33U2JH6.J5.				22.2 556 ..114					
220		10.0			D221G39U2JH6.J5.				22.2 556 ..214					
330		12.0			D331G47U2JH6.J5.				22.2 556 ..314					
CLASS 1 N1500														
18	± 2 %	5.0			5.0				4.0	D180G20P3KH6.J5.	06	08	10	22.2 586 ..154
22			D220G20P3KH6.J5.	22.2 586 ..204										
33			D330G20P3KH6.J5.	22.2 586 ..304										
47			D470G20P3KH6.J5.	22.2 586 ..404										
68			D680G20P3KH6.J5.	22.2 586 ..604										
100		6.5	D101G25P3KH6.J5.	22.2 586 ..014										
150		7.5	D151G29P3KH6.J5.	22.2 586 ..114										
220		8.5	D221G33P3KH6.J5.	22.2 586 ..214										
330		10.0	D331G39P3KH6.J5.	22.2 586 ..314										
470		11.0	D471G43P3KH6.J5.	22.2 586 ..414										
560		12.0	D561G47P3KH6.J5.	22.2 586 ..514										

Notes

- Maximum thickness 4.0 mm.
- 2.5 mm lead spacing is available on request. Straight leads leadstyle L2. Digit 14 (L) and 15 (2) Clear Text Code
- SH = seated height.
- Packaging codes refer to inward kinked leads. Other styles available on request.
- 3rd digit to complete RoHS catalog number. 8th and 9th digit of the catalog number to be completed with the packaging code.

PACKAGING				
D _{max} (mm)	SIZE CODE	PACKAGING QUANTITIES		
		BULK	REEL	AMMO
5.0 (0.20")	20	1000	2500	2000
6.5 (0.25")	25			
7.5 (0.29")	29			
8.5 (0.33")	33			
10.0 (0.39")	39			
11.0 (0.43")	43			
12.0 (0.47")	47			

Note

- The capacitors are supplied in bulk packaging (cardboard boxes), in tape on reel or in ammpack.



Kinked capacitors on tape, lead spacing 5.0 mm (0.2").

DIMENSIONS OF TAPE			
SYMBOL	PARAMETER	DIMENSIONS (mm)	
		NOMINAL	TOLERANCE
D	body diameter	11.0 maximum	-
d	lead diameter	0.6	± 0.05
P	pitch between capacitors	12.7	± 1.0
P ₀	feed-hole pitch	12.7	± 0.3; note 1
ΔP	plane deviation	1.0 maximum	-
P ₁	feed-hole centre to lead centre	3.85	± 0.7; note 2
P ₂	feed-hole centre to component centre	6.35	± 1.3; note 2
F	lead spacing	5.0	+ 0.6 - 0.4
Δh	component alignment	0	± 1.0
Δs	deviation along tape, left or right	0	± 1.0
W	tape width	18.0	+ 1.0 - 0.5
W ₀	hold-down tape width	5.0 minimum	-
W ₁	hole position	9.0	+ 0.75 - 0.5
W ₂	hold-down tape margin	3.0 maximum	-
H ₀	height to seating plane	16.0	± 0.5
H ₁	maximum component height	32.0	-
e	lead end protrusion	1.0 maximum	-
L	maximum length of snapped lead	11.0	-
D ₀	feed-hole diameter	4.0	± 0.2
t	total tape thickness	0.9 maximum	-
t ₁	maximum thickness of tape and wires	1.5 maximum	-

Notes

1. Cumulative pitch error: $\pm \leq 1 \text{ mm} / 20 \text{ pitches}$.
2. Obliquity maximum 3°.

LV 100 V Narrow Tolerance

Vishay BCcomponents


Ceramic Disc Capacitors
Class 1, 100 V (DC) Narrow Tolerance



REEL AND TAPE DATA in millimeters



Reel with capacitors on tape.



Ammopack with capacitors on tape.



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.