







LENGTH	
74546-4080	0.5M
74546-4081	1M
74546-4082	2M
74546-4083	3M
74546-4084	4M
74546-4085	5M
74546-4086	6M
74546-4087	7M

NOTES:

- MATERIAL =
BACKSHELL - ZINC DIECAST
PULL - NYLON
- LENGTH= SEE TABLE
- ELECTRICAL PERFORMANCE PER PCI EXPRESS
EXTERNAL CABLING SPEC, REV 1.0
- X8 PLUG MATES TO RECEPTACLE 75586-0002,
AND EMI GUIDE HOUSING ASSY. 74540-0101
- X4 PLUG MATES TO RECEPTACLE 75586-0010
AND EMI GUIDE HOUSING ASSY. 74540-0401.
- THIS PRODUCT MEETS THE RESTRICTIONS OF HAZARDOUS SUBSTANCES
IN ELECTRICAL AND ELECTRONIC EQUIPMENT (RoHS) DIRECTIVE
(2002/95/EC).


IPASS™ IS A TRADEMARK OF MOLEX

ENTER DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: USY2007-0450		2007/05/23		mm		MM ONLY		1:1		METRIC		THIRD ANGLE PROJECTION	
DRAWN: JERWIN		2007/06/01		INCH		DRAWN BY		DATE		TITLE		IPASS PCIE TRANSITION CABLE X4 - X8	
CHKD: BREED		2007/06/18		4 PLACES ± ---		BAREED		2006/03/22		MOLEX		MOLEX INCORPORATED	
APPR: DDOYE		2007/06/18		3 PLACES ± ---		CHECKED BY		DATE		DOCUMENT NO.		SD-74546-408	
				2 PLACES ± 0.13		DDOYE		2006/03/22		SHEET NO.		1 OF 3	
				1 PLACE ± 0.25		APPROVED BY		DATE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
				ANGULAR ± 1/2°		DDOYE		2006/03/22					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		SEE TABLE					
						SIZE							
						B							



IPASS IS TM A TRADEMARK OF MOLEX

ENTER DESCRIPTION EC NO: USY2007-0450 DRWN:JERWIN 2007/05/23 CHKD:BREED 2007/06/01 APPR:DDOYE 2007/06/18 A	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION				
			MM ONLY		1:1	METRIC					
			mm	INCH	DRAWN BY		DATE		TITLE		
			4 PLACES	± ---	± ---	BAREED		2006/03/22		IPASS PCIE	
			3 PLACES	± ---	± ---	CHECKED BY		DATE		TRANSITION CABLE	
			2 PLACES	± 0.13	± ---	DDOYE		2006/03/22		X4 - X8	
			1 PLACE	± 0.25	± ---	APPROVED BY		DATE			
			ANGULAR ±1/2°		DDOYE		2006/03/22		MOLEX INCORPORATED		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.			SHEET NO.	
					SEE CHART		SD-74546-408			2 OF 3	
REV		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
		B									



CABLE GAUGE	24	26	28
A. CABLE DIAMETER	10.4	9.3	8.4
B. MINIMUM OUTER RADIUS	46.9	41.7	37.7
C. FACEPLATE TO OUTER RADIUS	102.2	97.0	93.0

IPASS™ IS A TRADEMARK OF MOLEX

ENTER DESCRIPTION EC NO: USY2007-0450 DRWN: JERWIN 2007/05/23 CHKD: BREED 2007/06/01 APPR: DDOYE 2007/06/18 A	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY BAREED	DATE 2006/03/22	TITLE IPASS PCIE TRANSITION CABLE X4 - X8			
			4 PLACES	± ---	± ---	CHECKED BY DDOYE	DATE 2006/03/22				
			3 PLACES	± ---	± ---	APPROVED BY DDOYE	DATE 2006/03/22				
			2 PLACES	± 0.13	± ---	MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-74546-408			SHEET NO. 3 OF 3
			1 PLACE	± 0.25	± ---						
			ANGULAR ±1/2°			MOLEX MOLEX INCORPORATED					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								