


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER*	USE WITH THESE CABLE TIE CROSS SECTIONS	DIMENSION			WEIGHT lbs/100 pcs (g)/100 pcs
		'A'	'B'	'C'	
ABM2S-A	MINIATURE INTERMEDIATE STANDARD	1.00 (25.4)	1.00 (25.4)	.165 (4.2)	0.23 (107)



NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

TO APPLY MOUNTS:

1. REMOVE MOUNT FROM THE PROTECTIVE LINER.
2. PLACE IN DESIRED LOCATION.
3. APPLY PRESSURE TO TOP SURFACE OF MOUNT.

NOTES:

- 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2. MOUNTS PROVIDED IN STRIPS OF TWO FOR EASY REMOVAL FROM LINER.
- 3. MOUNT HAS CONTINUOUS OPERATION TEMPERATURE OF 120°F (49°C).

ADHESIVE BACKING:
PRESSURE SENSITIVE FOAM TAPE
0.0411.0) THICK WITH PROTECTIVE
LINER. MOUNT IS DESIGNED TO
SUPPORT 0.5 LBS. (227g) MAX.
WEIGHT ON A CLEAN, DRY, SMOOTH,
GREASE-FREE SURFACE.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS
603597HJ_DC_GB0239CF/00B

 <p>PANDUIT CORP. TINLEY PARK, ILLINOIS</p> <p>ABM2S-A ADHESIVE BACKED MOUNT</p>											
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± 0.05 (1.31) (.XXX) ± 0.010 (0.25) (.XX) ± 0.02 (0.51) ANGLES ± 5°						UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.					
DRAWN BY MJK DATE 11/3/94 CHG'D KLN						MATERIAL: ABS SCALE NONE DRAWING NO. GB0239CF SIZE A					
00B	02/24/09	GDH	REVISED DRAWING FORMAT, ADDED DIMENSIONS IN TABLE						GB0239CF		
9	3/3/05	JAD	REMOVE ABM2S						9		
8	7/9/03	JAD	CHANGED TOLERANCE ON .203 AND .067 DIMENSION FROM .010 (.25) TO .015 (.38)						8		
7	5/27/03	JAD	CORRECTED WINDOW WIDTH DIMENSION						7		
REV	DATE	BY	CHK	DESCRIPTION			ECN - R	CUST	SUP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ABM2S-A-D14](#) [ABM2S-AT-X0](#)