







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
H	-		M2	ECO-14-008965	02Dec13	CW
						SH

- NOTES:
1. TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.15
2. FOR APPLICATION INFORMATION SEE AMP SPEC. 114-19019.
3. FOR PERFORMANCE REQUIREMENTS SEE AMP SPEC. 108-19064




PRINTED CIRCUIT BOARD LAYOUT

[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.05
PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL.



800 PCS. ON A 60cm. DIA. REEL	8 POSITIONS/ 8 CONTACTS.	IN CONTACT AREA: 1.2 μ m MIN. SEL. GOLD OVER 1.2 μ m MIN. NICKEL	HOUSING: PBT,UL 94V-0 COLOR: BLACK	216550-2
		SOLDER TINES: 2.0 μ m MIN. TIN OVER 1.2 μ m MIN. NICKEL	HOUSING: PBT,UL 94V-HB COLOR: BLACK CONTACTS: PHOSPHOR BRONZE	216550-1
PACKAGING	REMARKS	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.v.LIEMPT 22JAN92		 TE Connectivity			
		CHK C.STERKEN -					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD L.V.SOEST -		MODULAR JACK, 8 POS. TOP ENTRY, SMALL SIZE WITH PANEL STOPS, FOR PRINTED CIRCUIT BOARDS			
		PRODUCT SPEC -					
		APPLICATION SPEC -					
		WEIGHT -					
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C=216550	RESTRICTED TO -
CUSTOMER DRAWING				SCALE -	SHEET 1 of 2	REV M3	

D

C

B

A

4






3

2


1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
H	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1/2			



THE SAME AS 216550-1, BUT NO PANEL STOP	HOUSING: PBT,UL 94V-HB GREY-RAL 7035	216550-6		
	CONTACTS: PHOSPHOR BRONZE			
	HOUSING: PBT,UL 94V-HB YELLOW Pantone 115U	216550-5		
	CONTACTS: PHOSPHOR BRONZE			
	HOUSING: PBT,UL 94V-HB COLOR: BLACK	216550-4		
	CONTACTS: PHOSPHOR BRONZE			
PACKAGING	REMARKS	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J.v.LIEMPT	22JAN92	 TE Connectivity					
			CHK C.STERKEN	—						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L.V.SOEST	NAME					
		0 PLC ± —		PRODUCT SPEC	MODULAR JACK, 8 POS. TOP ENTRY, SMALL SIZE WITH PANEL STOPS, FOR PRINTED CIRCUIT BOARDS					
		1 PLC ± —		—						
		2 PLC ± —		APPLICATION SPEC						
		3 PLC ± —		—						
		4 PLC ± —		—						
ANGLES ± —		FINISH		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL				WEIGHT —	A2	00779	C=216550	—		
SEE TABLE		SEE TABLE		CUSTOMER DRAWING				SCALE —	SHEET 2 of 2	REV M3

D

C

B

A

216550