


LOB SERIES

LOW RESISTANCE METAL ELEMENT RESISTOR

- Ultra low resistance values (0.005Ω to 0.1Ω)
- Available in 1-watt, 3-watt and 5-watt rated packages
- Tolerances from $\pm 1\%$ to $\pm 5\%$
- Inherently non-inductive ($\leq 0.02\mu\text{H}$ @ 0.5MHz)
- Low temperature coefficient of resistance
- High stability over life
- Lead free ROHS compliant construction available



DESCRIPTION:

LOB Series power precision metal element resistors feature resistance values down to 0.005Ω with virtually no inductance. Available in 1-, 3- and 5-watt rated axial leaded packages, these resistors are compatible with automatic insertion equipment.

APPLICATIONS:

- Switchmode and linear power supplies.
- Automotive current-sensing circuits
- Instrumentation
- Regulators

CONSTRUCTION:

LOB Series resistors feature tinned copper leads welded directly to a low-temperature coefficient resistance element in a highly automated proprietary process. The leaded resistor elements are then encapsulated in a molding com-

ABSOLUTE MAXIMUM RATINGS:

CHARACTERISTIC	LOB-1	LOB-3	LOB-5	Units
Continuous power dissipation @ 25°C in free air	1	3	5	Watts
Overload power for 5 seconds	5	15	25	Watts
Maximum working voltage	$\sqrt{1 \times R}$	$\sqrt{3 \times R}$	$\sqrt{5 \times R}$	Volts
Maximum storage temperature	175	175	175	$^\circ\text{C}$

*Power Dissipation - The maximum wattage rating depends upon the amount of heat which can be transferred to the surroundings while not exceeding the maximum element temperature. Ambient air temperature, velocity of cooling air, thermal resistance of heat, and the temperature of surrounding objects will affect this transfer, and must be taken into account when

GENERAL SPECIFICATIONS - ENVIRONMENTAL TESTING*:

TEST PARAMETERS	MIL-STD 202	MAX $\% \Delta R$ *	Unit
Load Life (2,000 hours)	Method 108	$\pm 1\%$	$\% \Delta R$
Thermal Shock	Method 107	$\pm 1\%$	$\% \Delta R$
Vibration	Method 204	$\pm 0.5\%$	$\% \Delta R$
Mechanical Shock	Method 213	$\pm 0.5\%$	$\% \Delta R$
Dielectric Strength	Method 301	$\pm 0.5\%$	$\% \Delta R$
Insulation Resistance	Method 302	$> 10^{11}$	Ohms

* ± 0.0005 ohm allowance for test/contact error.

General Note

IRC reserves the right to make changes in product specification without notice or liability. All information is subject to IRC's own data and is considered accurate at time of going to print.

WIREWOUND AND FILM TECHNOLOGIES DIVISION


736 Greenway Road • Boone, North Carolina 28607-1860 • Tel: 828-264-8861 • Fax: 828-264-8866 • www.irctt.com




A subsidiary of
TT electronics plc

LOB DIMENSIONS (Inches and (mm)):


Style	L	D	C	I	d
LOB-1	0.390 ±0.010 (9.9 ±0.3)	0.140 ±0.008 (3.6 ±0.2)	1.31 (33.274)	1.50 ±0.125 (38.1 ±3.2)	0.0305 ±0.002 (0.813 ±0.051)
LOB-3	0.560 ±0.010 (14.224 ±0.254)	0.210 ±0.010 (5.334 ±0.254)	1.31 (33.274)	1.375 ±0.125 (34.925 ±3.175)	0.0305 ±0.002 (0.813 ±0.051)
LOB-5	0.920 ±0.010 (23.368 ±0.254)	0.330 ±0.010 (8.382 ±0.254)	1.670 (42.418)	1.250 ±0.125 (31.750 ±3.175)	0.040 ±0.002 (1.016 ±0.051)



POWER DERATING PERCENTAGE VS. FREE AIR AMBIENT TEMPERATURE:



TEMPERATURE COEFFICIENT OF RESISTANCE VS. RESISTANCE VALUE:



HOW TO ORDER:

To order, specify style, resistance value, tolerance and package type as in the following example:

LOB-3 0.01Ω 1% LF LT

StylePackaging

LT (Lead Tape) 500 pcs. min.
LOB-1 (1 watt)
LOB-3 (3 watt)
LOB-5 (5 watt)

Resistance Value

0.005Ω 0.02Ω 0.04Ω 0.08Ω
0.01Ω 0.025Ω 0.05Ω 0.1Ω
0.015Ω 0.03Ω 0.07Ω Contact factory for other values

Tolerance

5%, 3%, 1% - All styles/values

Packaging

LT (Lead Tape) 500 pcs. min.
LOB-1 3500pcs. max.
LOB-3 1250 pcs. max.
LOB-5 800 pcs. max.

BLK (Bulk Pack) 500/box
packed loose in box

Lead-Free Construction

General Note

IRC reserves the right to make changes in product specification without notice or liability.
All information is subject to IRC's own data and is considered accurate at time of going to print.

WIREWOUND AND FILM TECHNOLOGIES DIVISION

736 Greenway Road • Boone, North Carolina 28607-1860 • Tel: 828-264-8861 • Fax: 828-264-8866 • www.irctt.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT electronics:

[LOB3R040J](#) [LOB3R020J](#) [LOB3R025J](#) [LOB1R070J](#) [LOB1R005J](#) [LOB5R020J](#) [LOB5R020F](#) [LOB5R025J](#)
[LOB5R010J](#) [LOB3R010F](#) [LOB3R015J](#) [LOB3R025FTR](#) [LOB3R010FTR](#) [LOB5R070J](#) [LOB5R020FTR](#) [LOB3R080J](#)
[LOB3R050FTR](#) [LOB3R030H](#) [LOB3R030J](#) [LOB5R080J](#) [LOB1R050J](#) [LOB3R080HTR](#) [LOB1R025J](#) [LOB3R005F](#)
[LOB-10.051%BLK](#) [LOB5R100J](#) [LOB5R100F](#) [LOB5R050J](#) [LOB1R030J](#) [LOB5R040J](#) [LOB3R050J](#) [LOB1R020J](#)
[LOB1R080J](#) [LOB5R030J](#) [LOB3R050JLF](#) [LOB5R050JLF](#) [LOB3R030JLF](#) [LOB5R030JLF](#) [LOB1R025JLF](#)
[LOB5R025JLF](#) [LOB3R025JLF](#) [LOB3R010JLF](#) [LOB5R010JLF](#) [LOB1R010JLF](#) [LOB5R033FLF](#) [LOB5R040JLF](#)
[LOB1R040JLF](#) [LOB3R040JLF](#) [LOB5R100JLF](#) [LOB5R020JLF](#) [LOB3R020JLF](#) [LOB3R050FLFTR](#) [LOB3R025FLFTR](#)
[LOB1R005FLFTR](#) [LOB3R005J](#) [LOB1R015J](#) [LOB3R030FLF](#) [LOB1R005FTR](#) [LOB3R005FTRLF](#) [LOB3R010FLF](#)
[LOB3R020FLF](#) [LOB3R050FLF](#) [LOB3R100FLF](#) [LOB5R005F](#) [LOB5R010F](#) [LOB5R030F](#) [LOB1R080JLF](#)
[LOB3R080JLF](#) [LOB3R070JLF](#) [LOB5R070JLF](#) [LOB1R070JLF](#) [LOB3R015JLF](#) [LOB5R005JLF](#) [LOB5R025FLF](#)
[LOB5R100FLF](#)