

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0366440003

Status:

Active

Overview:

MLX Power Connectors

Description:

2.13mm Diameter MLX Pin and Socket Receptacle, 3 Circuit, PA Polyamide Nylon 6/6 94V-2, Glow-Wire Capable

Documents:

[Drawing \(PDF\)](#)

[3D Model \(PDF\)](#)

[3D Model](#)

[Product Specification PS-36644-001-001 \(PDF\)](#)


[Packaging Specification PK-42022-XX-001 \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	36644
Application	Power, Wire-to-Wire
Comments	This Molex product is manufactured from material that has the following ratings, tested by independent agencies :. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety; section 30 Resistance to heat and fire.<P><P>The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s).<P>If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.
Overview	MLX Power Connectors
Product Name	MLX
UPC	800756935164

Physical	
Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.171/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.35mm
Pitch - Termination Interface	6.35mm



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

36644 Series

Mates With

2.13mm Diameter MLX Plug Housing [42021](#) , [36643](#)

Use With

MLX Crimp Terminal [42023](#) , [42024](#)

Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C
Electrical	
Current - Maximum per Contact	20.0A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-42022-XX-001
Product Specification	PS-36644-001-001
Sales Drawing	SD-36644-009, SD-42022-XX

This document was generated on 08/17/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION