


0805CX MINIATURE RF CHIP INDUCTORS

Designed for Wireless Products




- Wirewound ceramic core construction
- High Q values and self-resonant frequency
- Gold terminations
- Industry standard 0805 (2012) surface mount land pattern


Electrical Specifications @ 25°C

Part Number	Inductance ¹ (nH)	Standard Tolerance	Optional Tolerance	Q ² (MIN)	SRF ³ (MHz MIN)	R _{DC} ⁴ (Ω MAX)	I _{DC} ⁵ (mA MAX)	Part Code
PE-0805CX030KTG	3.3 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	37 @ 1500 MHz	5000	0.060	600	A
PE-0805CX060KTG	6.8 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	46 @ 1000 MHz	5000	0.150	600	B
PE-0805CX080KTG	8.2 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	47 @ 1000 MHz	3900	0.130	600	C
PE-0805CX120KTG	12 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	50 @ 500 MHz	2900	0.130	600	D
PE-0805CX150KTG	15 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	50 @ 500 MHz	2700	0.150	600	E
PE-0805CX180KTG	18 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	50 @ 500 MHz	2600	0.130	600	F
PE-0805CX220KTG	22 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	55 @ 500 MHz	2200	0.130	500	G
PE-0805CX270KTG	27 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	55 @ 500 MHz	2000	0.230	500	H
PE-0805CX330KTG	33 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	58 @ 500 MHz	1800	0.180	500	J
PE-0805CX390KTG	39 @ 250 MHz	± 10% (K)	±5%, ±2%, ±1%	60 @ 500 MHz	1600	0.230	500	K
PE-0805CX470KTG	47 @ 200 MHz	± 10% (K)	±5%, ±2%, ±1%	60 @ 500 MHz	1650	0.250	500	L
PE-0805CX560KTG	56 @ 200 MHz	± 10% (K)	±5%, ±2%, ±1%	60 @ 500 MHz	1300	0.160	500	M
PE-0805CX680KTG	68 @ 200 MHz	± 10% (K)	±5%, ±2%, ±1%	60 @ 500 MHz	1350	0.180	500	N
PE-0805CX820KTG	82 @ 150 MHz	± 10% (K)	±5%, ±2%, ±1%	60 @ 500 MHz	1300	0.360	400	O
PE-0805CX101KTG	100 @ 150 MHz	± 10% (K)	±5%, ±2%, ±1%	55 @ 500 MHz	1100	0.360	400	P
PE-0805CX121KTG	120 @ 150 MHz	± 10% (K)	±5%, ±2%, ±1%	45 @ 250 MHz	1100	0.560	350	R
PE-0805CX151KTG	150 @ 100 MHz	± 10% (K)	±5%, ±2%, ±1%	50 @ 250 MHz	900	0.560	350	S
PE-0805CX181KTG	180 @ 100 MHz	± 10% (K)	±5%, ±2%, ±1%	50 @ 250 MHz	875	0.690	300	T
PE-0805CX221KTG	220 @ 100 MHz	± 10% (K)	±5%, ±2%, ±1%	45 @ 250 MHz	800	0.850	300	U
PE-0805CX271KTG	270 @ 100 MHz	± 10% (K)	±5%, ±2%, ±1%	40 @ 100 MHz	800	0.900	300	X
PE-0805CX331KTG	330 @ 100 MHz	± 10% (K)	±5%, ±2%, ±1%	40 @ 100 MHz	775	1.300	300	Y
PE-0805CX391KTG	390 @ 100 MHz	± 10% (K)	±5%, ±2%, ±1%	40 @ 100 MHz	725	1.700	300	A1
PE-0805CX471KTG	470 @ 100 MHz	± 10% (K)	±5%, ±2%, ±1%	38 @ 100 MHz	600	3.250	240	B1
PE-0805CX561KTG	560 @ 100 MHz	± 10% (K)	±5%, ±2%, ±1%	40 @ 100 MHz	600	3.100	240	C1
PE-0805CX681KTG	680 @ 50 MHz	± 10% (K)	±5%, ±2%, ±1%	32 @ 50 MHz	550	3.500	240	D1

Mechanical



Suggested SMD Pad Layout



Weight 0.012 grams
Tape & Reel 2000/reel

Dimensions: $\frac{\text{Inches}}{\text{mm}}$


Unless otherwise specified
all tolerances are ± $\frac{.010}{0.25}$

0805CX MINIATURE RF CHIP INDUCTORS

Designed for Wireless Products



Typical Q vs. Frequency



NOTES:

1. Inductance measured using a HP4191A RF Impedance Analyzer.
2. Q measured using a HP4291A RF Impedance Analyzer with a HP16193A Test Fixture.
3. SRF measured using a HP8753C Network Analyzer.
4. R_{DC} measured using a Valhalla Scientific model 4100 ATC Digital Ohmmeter.
5. Based on a 15°C maximum temperature rise.
6. Sample Kit Part Number: PE-0805CXKIT-G.
7. S-parameters and Q & Inductance vs. Frequency Information available on 3.5" disk. Please request **AN944-1**.

Part Number Legend

PE — **0805** **C** **X**

PACKAGE STYLE

CORE MATERIAL
C = Ceramic (Alumina)

PROFILE
X = Standard

121 **K** **T** **G**

INDUCTANCE (nH)
1st 2 digits are significant.
3rd digit is multiplier.

TOLERANCE
G = $\pm 2\%$
J = $\pm 5\%$
K = $\pm 10\%$
M = $\pm 20\%$

TERMINATION
G = Tungsten/Nickel/Gold Flash

PACKAGING
T = Tape & Reel (2000 Pieces/
7" reel/8 mm wide tape/4 mm pitch)
B = Bulk/Partial Reel

EXAMPLE: 0805 Size, Ceramic Core, Standard Height, 120 nH, 10% Tolerance, Tape & Reel, Gold Termination

For More Information :

Corporate

12220 World Trade Drive
San Diego, CA 92128
Tel: 619 674 8100
FAX: 619 674 8262
<http://www.pulseeng.com>
Quick-Facts: 619 674 9672

Europe

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
Tel: 44 1483 401700
FAX: 44 1483 401701

Asia

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
Tel: 65 287 8998
FAX: 65 280 0080

Distributor

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.