




FCIconnect.com

PRODUCT NUMBER	SERIES NAME	PITCH
20020004-CXXXXXXLF	01-350	3.50 mm



N = Number of Poles
 Dim A = $N \times 3.5[.138]$
 Dim B = $(N-1) \times 3.5[.138]$

POLES	Dim A	Dim B
2-6p	$\pm 0.15[.006]$	
7-12p	$\pm 0.20[.008]$	
13-18p	$\pm 0.25[.010]$	
19-24p	$\pm 0.30[.012]$	

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
L					angles X. $\pm 0.5[.020]$ X.X $\pm 0.3[.012]$ X $\pm 1^\circ$ X.XX $\pm 0.1[.004]$	scale	TERMINAL BLOCK PLUGABLE, PLUG, SIGNAL, W/O FLANGE
			dr	BEER FU	062509		dwg no
			enr	BEER FU	062509		sheet 2 of 3 size
			chr	GARY HSIEH	062509		20020004 A4
			app	JOSEPH HSIA	062509		type
sheet index	revision sheet						CUSTOMER Drawing



Copyright FCI.



FCIconnect.com





1 2

3

4

PRODUCT NUMBER	SERIES NAME	PITCH
20020004-DXXXXXXLF	01-381	3.81 mm

1.91[.075] Dim B
3.81[.150]
2p to 6p with wedge, above 7p
without wedge (including 7p)



N = Number of Poles
Dim A = $N \times 3.81[.150]$
Dim B = $(N-1) \times 3.81[.150]$

POLES	Dim A	Dim B
2-6p	$\pm 0.15[.006]$	
7-12p	$\pm 0.20[.008]$	
13-18p	$\pm 0.25[.010]$	
19-24p	$\pm 0.30[.012]$	

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn	no	dr	date			title
L							TERMINAL BLOCK
				angles	X. $\pm 0.5[.020]$		PLUGABLE, PLUG, SIGNAL, W/O FLANGE
				tolerances unless otherwise specified	X.X $\pm 0.3[.012]$		dwg no
				X* $\pm 1^\circ$	X.XX $\pm 0.1[.004]$	scale	sheet 3 of 3 size
				dr	BEER FU	062509	20020004
				enr	BEER FU	062509	A4
				chr	GARY HSIEH	062509	
				appd	JOSEPH HSIA	062509	
sheet index	revision	sheet					type
							CUSTOMER Drawing