





STRIP MATERIAL NUMBER	FINISH
84525-0025	SELECTIVE TIN 100μ INCH MINIMUM OVER NICKEL 80μ INCH MINIMUM OVERALL
84525-0046	SELECTIVE HARD GOLD 30μ INCH MINIMUM WITH SELECTIVE TIN 100μ INCH MINIMUM OVER NICKEL 50μ INCH MINIMUM OVERALL



WIRE INSULATION O.D. RANGE $.095-.150$ / $2.41-3.81$



Section Y-Y
Scale 5:1
INSULATION CRIMP



Section W-W
Scale 5:1
CONDUCTOR CRIMP

NOTES:

1. TERMINAL MATERIAL: COPPER ALLOY, .0118/0.300 THICK. FINISH: SEE CHART.
2. HOOD MATERIAL: STAINLESS STEEL, .006/0.15 THICK.
3. STRIP PARTS ARE REELED 3000 PARTS PER REEL AS SHOWN ABOVE.
4. TERMINAL FOR USE WITH SERIES XRC CONNECTOR ASSEMBLIES.
5. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.

UPDATE LENGTH EC NO: IPG2012-0063 DRAWN: WLEUNG CHKD: APPR: DTTITUS	2011/12/06 2012/01/09	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 				
					mm	INCH	DRAWN BY MODELL	DATE 2009/04/09	TITLE XRC SOCKET W/SNAP WINDOW 14-18AWG .095"-.150" WIRE DIA MOLEX INCORPORATED					
				4 PLACES	± ---	± ---	CHECKED BY RDEROSS	DATE 2009/04/09						
				3 PLACES	± ---	± .005	APPROVED BY	DATE						
				2 PLACES	± .13	± ---	DTITUS	2010/12/06						
				1 PLACE	± ---	± ---	MATERIAL NO.		DOCUMENT NO.	SHEET NO.				
				ANGULAR ± ---°			SEE CHART		SD-84525-007		1 OF 1			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					