

# RF Power Field Effect Transistors

## N-Channel Enhancement-Mode Lateral MOSFETs

Designed for CDMA and multicarrier base station applications with frequencies from 1805 to 1880 MHz. Can be used in Class AB and Class C for all typical cellular base station modulation formats.

- Typical Doherty Single-Carrier W-CDMA Performance:  $V_{DD} = 30$  Volts,  $I_{DQA} = 800$  mA,  $V_{GSB} = 1.3$  V,  $P_{out} = 72$  Watts Avg., IQ Magnitude Clipping, Channel Bandwidth = 3.84 MHz, Input Signal PAR = 9.9 dB @ 0.01% Probability on CCDF.

| Frequency | $G_{ps}$<br>(dB) | $\eta_D$<br>(%) | Output PAR<br>(dB) | ACPR<br>(dBc) |
|-----------|------------------|-----------------|--------------------|---------------|
| 1805 MHz  | 15.9             | 44.8            | 6.9                | -31.7         |
| 1840 MHz  | 16.1             | 43.4            | 7.0                | -31.7         |
| 1880 MHz  | 16.0             | 43.7            | 6.7                | -32.2         |

- Capable of Handling 10:1 VSWR, @ 32 Vdc, 1840 MHz, 280 Watts CW Output Power (2 dB Input Overdrive from Rated  $P_{out}$ )
- Typical  $P_{out}$  @ 3 dB Compression Point  $\approx$  280 Watts CW

### Features

- Production Tested in a Symmetrical Doherty Configuration
- 100% PAR Tested for Guaranteed Output Power Capability
- Characterized with Large-Signal Load-Pull Parameters and Common Source S-Parameters
- Internally Matched for Ease of Use
- Integrated ESD Protection
- Greater Negative Gate-Source Voltage Range for Improved Class C Operation
- Designed for Digital Predistortion Error Correction Systems
- In Tape and Reel. R6 Suffix = 150 Units per 56 mm, 13 inch Reel.

**Table 1. Maximum Ratings**

| Rating                                                                     | Symbol    | Value       | Unit      |
|----------------------------------------------------------------------------|-----------|-------------|-----------|
| Drain-Source Voltage                                                       | $V_{DSS}$ | -0.5, +65   | Vdc       |
| Gate-Source Voltage                                                        | $V_{GS}$  | -6.0, +10   | Vdc       |
| Operating Voltage                                                          | $V_{DD}$  | 32, +0      | Vdc       |
| Storage Temperature Range                                                  | $T_{stg}$ | -65 to +150 | °C        |
| Case Operating Temperature                                                 | $T_C$     | 150         | °C        |
| Operating Junction Temperature (1,2)                                       | $T_J$     | 225         | °C        |
| CW Operation @ $T_C = 25^\circ\text{C}$<br>Derate above $25^\circ\text{C}$ | CW        | 446<br>4.5  | W<br>W/°C |


**Table 2. Thermal Characteristics**

| Characteristic                                                                                                                                                                                                                                                 | Symbol          | Value (2,3)  | Unit |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|--------------|------|
| Thermal Resistance, Junction to Case<br>Case Temperature $74^\circ\text{C}$ , 72.5 W CW, 30 Vdc, $I_{DQA} = 800$ mA, $V_{GSB} = 1.3$ V, 1880 MHz<br>Case Temperature $90^\circ\text{C}$ , 260 W CW(4), 30 Vdc, $I_{DQA} = 800$ mA, $V_{GSB} = 1.3$ V, 1880 MHz | $R_{\theta JC}$ | 0.27<br>0.25 | °C/W |


- Continuous use at maximum temperature will affect MTTF.
- MTTF calculator available at <http://www.freescale.com/rf>. Select Software & Tools/Development Tools/Calculators to access MTTF calculators by product.
- Refer to AN1955, *Thermal Measurement Methodology of RF Power Amplifiers*. Go to <http://www.freescale.com/rf>. Select Documentation/Application Notes - AN1955.
- Exceeds recommended operating conditions. See CW operation data in Maximum Ratings table.

## MRF8P18265HR6 MRF8P18265HSR6


1805-1880 MHz, 72 W AVG., 30 V  
SINGLE W-CDMA  
LATERAL N-CHANNEL  
RF POWER MOSFETs



CASE 375I-04  
NI-1230-8  
MRF8P18265HR6



CASE 375J-03  
NI-1230S-8  
MRF8P18265HSR6



**Figure 1. Pin Connections**

**Table 3. ESD Protection Characteristics**

| Test Methodology                      | Class |
|---------------------------------------|-------|
| Human Body Model (per JESD22-A114)    | 2     |
| Machine Model (per EIA/JESD22-A115)   | A     |
| Charge Device Model (per JESD22-C101) | IV    |

**Table 4. Electrical Characteristics** ( $T_A = 25^\circ\text{C}$  unless otherwise noted)

| Characteristic | Symbol | Min | Typ | Max | Unit |
|----------------|--------|-----|-----|-----|------|
|----------------|--------|-----|-----|-----|------|

**Off Characteristics** <sup>(1)</sup>

|                                                                                                   |           |   |   |    |                 |
|---------------------------------------------------------------------------------------------------|-----------|---|---|----|-----------------|
| Zero Gate Voltage Drain Leakage Current<br>( $V_{DS} = 65\text{ Vdc}$ , $V_{GS} = 0\text{ Vdc}$ ) | $I_{DSS}$ | — | — | 10 | $\mu\text{Adc}$ |
| Zero Gate Voltage Drain Leakage Current<br>( $V_{DS} = 30\text{ Vdc}$ , $V_{GS} = 0\text{ Vdc}$ ) | $I_{DSS}$ | — | — | 1  | $\mu\text{Adc}$ |
| Gate-Source Leakage Current<br>( $V_{GS} = 5\text{ Vdc}$ , $V_{DS} = 0\text{ Vdc}$ )              | $I_{GSS}$ | — | — | 1  | $\mu\text{Adc}$ |

**On Characteristics** <sup>(1)</sup>

|                                                                                                                  |              |     |      |     |     |
|------------------------------------------------------------------------------------------------------------------|--------------|-----|------|-----|-----|
| Gate Threshold Voltage<br>( $V_{DS} = 10\text{ Vdc}$ , $I_D = 200\text{ }\mu\text{Adc}$ )                        | $V_{GS(th)}$ | 1.1 | 1.9  | 2.6 | Vdc |
| Gate Quiescent Voltage<br>( $V_{DD} = 30\text{ Vdc}$ , $I_{DA} = 800\text{ mAdc}$ , Measured in Functional Test) | $V_{GS(Q)}$  | 1.8 | 2.6  | 3.3 | Vdc |
| Drain-Source On-Voltage<br>( $V_{GS} = 10\text{ Vdc}$ , $I_D = 2\text{ Adc}$ )                                   | $V_{DS(on)}$ | 0.1 | 0.15 | 0.3 | Vdc |

**Functional Tests** <sup>(2,3)</sup> (In Freescale Doherty Test Fixture, 50 ohm system)  $V_{DD} = 30\text{ Vdc}$ ,  $I_{DQA} = 800\text{ mA}$ ,  $V_{GSB} = 1.3\text{ V}$ ,  $P_{out} = 72\text{ W Avg.}$ ,  $f = 1880\text{ MHz}$ , Single-Carrier W-CDMA, IQ Magnitude Clipping, Input Signal PAR = 9.9 dB @ 0.01% Probability on CCDF. ACPR measured in 3.84 MHz Channel Bandwidth @  $\pm 5\text{ MHz}$  Offset.

|                                                          |          |      |       |       |     |
|----------------------------------------------------------|----------|------|-------|-------|-----|
| Power Gain                                               | $G_{ps}$ | 13.8 | 16.0  | 17.0  | dB  |
| Drain Efficiency                                         | $\eta_D$ | 41.0 | 43.7  | —     | %   |
| Output Peak-to-Average Ratio @ 0.01% Probability on CCDF | PAR      | 6.0  | 6.7   | —     | dB  |
| Adjacent Channel Power Ratio                             | ACPR     | —    | -32.2 | -28.0 | dBc |

**Typical Broadband Performance** <sup>(3)</sup> (In Freescale Doherty Test Fixture, 50 ohm system)  $V_{DD} = 30\text{ Vdc}$ ,  $I_{DQA} = 800\text{ mA}$ ,  $V_{GSB} = 1.3\text{ V}$ ,  $P_{out} = 72\text{ W Avg.}$ , Single-Carrier W-CDMA, IQ Magnitude Clipping, Input Signal PAR = 9.9 dB @ 0.01% Probability on CCDF. ACPR measured in 3.84 MHz Channel Bandwidth @  $\pm 5\text{ MHz}$  Offset.

| Frequency | $G_{ps}$<br>(dB) | $\eta_D$<br>(%) | Output PAR<br>(dB) | ACPR<br>(dBc) |
|-----------|------------------|-----------------|--------------------|---------------|
| 1805 MHz  | 15.9             | 44.8            | 6.9                | -31.7         |
| 1840 MHz  | 16.1             | 43.4            | 7.0                | -31.7         |
| 1880 MHz  | 16.0             | 43.7            | 6.7                | -32.2         |

- Each side of device measured separately.
- Part internally matched both on input and output.
- Measurement made with device in a symmetrical Doherty configuration.

(continued)

**Table 4. Electrical Characteristics** ( $T_A = 25^\circ\text{C}$  unless otherwise noted) (continued)

| Characteristic                                                                                                                                                                                         | Symbol             | Min | Typ   | Max | Unit                 |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|-----|-------|-----|----------------------|
| <b>Typical Performance</b> <sup>(1)</sup> (In Freescale Doherty Test Fixture, 50 ohm system) $V_{DD} = 30\text{ Vdc}$ , $I_{DQA} = 800\text{ mA}$ , $V_{GSB} = 1.3\text{ V}$ , 1805–1880 MHz Bandwidth |                    |     |       |     |                      |
| $P_{out}$ @ 1 dB Compression Point, CW                                                                                                                                                                 | P1dB               | —   | 224   | —   | W                    |
| $P_{out}$ @ 3 dB Compression Point, CW                                                                                                                                                                 | P3dB               | —   | 280   | —   | W                    |
| IMD Symmetry @ 17 W PEP, $P_{out}$ where IMD Third Order Intermodulation $\cong 30\text{ dBc}$<br>(Delta IMD Third Order Intermodulation between Upper and Lower Sidebands $> 2\text{ dB}$ )           | IMD <sub>sym</sub> | —   | 72    | —   | MHz                  |
| VBW Resonance Point<br>(IMD Third Order Intermodulation Inflection Point)                                                                                                                              | VBW <sub>res</sub> | —   | 88    | —   | MHz                  |
| Gain Flatness in 75 MHz Bandwidth @ $P_{out} = 72\text{ W Avg.}$                                                                                                                                       | G <sub>F</sub>     | —   | 0.4   | —   | dB                   |
| Gain Variation over Temperature<br>( $-30^\circ\text{C}$ to $+85^\circ\text{C}$ )                                                                                                                      | $\Delta G$         | —   | 0.01  | —   | dB/ $^\circ\text{C}$ |
| Output Power Variation over Temperature<br>( $-30^\circ\text{C}$ to $+85^\circ\text{C}$ ) <sup>(2)</sup>                                                                                               | $\Delta P_{1dB}$   | —   | 0.005 | —   | dB/ $^\circ\text{C}$ |

1. Measurement made with device in a symmetrical Doherty configuration.

2. Exceeds recommended operating conditions. See CW operation data in Maximum Ratings table.





Figure 2. MRF8P18265HR6(HSR6) Test Circuit Component Layout


Table 5. MRF8P18265HR6(HSR6) Test Circuit Component Designations and Values

| Part                               | Description                                 | Part Number          | Manufacturer |
|------------------------------------|---------------------------------------------|----------------------|--------------|
| C1, C2, C3, C4, C13, C14, C23, C24 | 15 pF Chip Capacitors                       | ATC600F150JT250XT    | ATC          |
| C5, C6, C11, C12                   | 10 $\mu$ F, 50 V Chip Capacitors            | GRM55DR61H106KA88L   | Murata       |
| C7, C8                             | 100 $\mu$ F, 50 V Chip Capacitors           | MCGPR50V107M8X11     | Multicomp    |
| C9, C10                            | 470 $\mu$ F, 63 V Chip Capacitors           | MCGPR63V477M13X26-RH | Multicomp    |
| C15, C16                           | 6.8 $\mu$ F Chip Capacitors                 | C4532X7RIH685KT      | TDK          |
| C17, C18                           | 2.2 pF Chip Capacitors                      | ATC600F2R2BT250XT    | ATC          |
| C19, C20                           | 0.8 pF Chip Capacitors                      | ATC600F0R8BT250XT    | ATC          |
| C21, C22                           | 0.3 pF Chip Capacitors                      | ATC600F0R3BT250XT    | ATC          |
| C25                                | 0.1 pF Chip Capacitor                       | ATC600F0R1BT250XT    | ATC          |
| R1                                 | 50 $\Omega$ , 4 W Chip Resistor             | CW12010T0050GBK      | ATC          |
| R2, R3                             | 10 $\Omega$ , 1/4 W Chip Resistors          | CRCW120610R0FKEA     | Vishay       |
| Z1                                 | 1900 MHz Band 90°, 3 dB Chip Hybrid Coupler | GCS351-HYB1900       | Soshin       |
| PCB                                | 0.020", $\epsilon_r = 3.5$                  | RF-35                | Taconic      |


## TYPICAL CHARACTERISTICS



**Figure 3. Output Peak-to-Average Ratio Compression (PARC) Broadband Performance @  $P_{out} = 72$  Watts Avg.**




**Figure 4. Intermodulation Distortion Products versus Two-Tone Spacing**




**Figure 5. Output Peak-to-Average Ratio Compression (PARC) versus Output Power**

## TYPICAL CHARACTERISTICS




**Figure 6. Single-Carrier W-CDMA Power Gain, Drain Efficiency and ACPR versus Output Power**




**Figure 7. Broadband Frequency Response**

## W-CDMA TEST SIGNAL



**Figure 8. CCDF W-CDMA IQ Magnitude Clipping, Single-Carrier Test Signal**



**Figure 9. Single-Carrier W-CDMA Spectrum**


$V_{DD} = 30 \text{ Vdc}$ ,  $I_{DQA} = 800 \text{ mA}$

| f<br>MHz | Max $P_{out}$ <sup>(1)</sup> |      | $Z_{source}$<br>$\Omega$ | $Z_{load}$<br>$\Omega$ |
|----------|------------------------------|------|--------------------------|------------------------|
|          | Watts                        | dBm  |                          |                        |
| 1805     | 195                          | 52.9 | $2.38 - j6.43$           | $1.31 - j2.51$         |
| 1840     | 195                          | 52.9 | $3.70 - j7.13$           | $1.21 - j2.50$         |
| 1880     | 190                          | 52.8 | $4.23 - j7.74$           | $1.24 - j2.51$         |

(1) Maximum output power measurement reflects pulsed 1 dB gain compression.

$Z_{source}$  = Test circuit impedance as measured from gate contact to ground.

$Z_{load}$  = Test circuit impedance as measured from drain contact to ground.



**Figure 10. Carrier Side Load Pull Performance — Maximum P1dB Tuning**


$V_{DD} = 30 \text{ Vdc}$ ,  $I_{DQA} = 800 \text{ mA}$

| f<br>MHz | Max Eff. <sup>(1)</sup><br>% | $Z_{source}$<br>$\Omega$ | $Z_{load}$<br>$\Omega$ |
|----------|------------------------------|--------------------------|------------------------|
|          |                              |                          |                        |
| 1805     | 69.3                         | $2.38 - j6.43$           | $3.10 - j1.22$         |
| 1840     | 68.9                         | $3.70 - j7.13$           | $2.59 - j1.37$         |
| 1880     | 68.3                         | $4.23 - j7.74$           | $2.47 - j1.17$         |

(1) Maximum output power measurement reflects pulsed 1 dB gain compression.


$Z_{source}$  = Test circuit impedance as measured from gate contact to ground.

$Z_{load}$  = Test circuit impedance as measured from drain contact to ground.



**Figure 11. Carrier Side Load Pull Performance — Maximum Efficiency Tuning**

## ALTERNATIVE PEAK TUNE LOAD PULL CHARACTERISTICS



NOTE: Load Pull Test Fixture Tuned for Peak P1dB Output Power @ 30 V

| f<br>(MHz) | P1dB  |      | P3dB  |      |
|------------|-------|------|-------|------|
|            | Watts | dBm  | Watts | dBm  |
| 1805       | 197   | 52.9 | 226   | 53.5 |
| 1845       | 194   | 52.9 | 223   | 53.5 |
| 1880       | 190   | 52.8 | 226   | 53.5 |


Test Impedances per Compression Level

| f<br>(MHz) |      | $Z_{source}$<br>$\Omega$ | $Z_{load}$<br>$\Omega$ |
|------------|------|--------------------------|------------------------|
| 1805       | P1dB | $2.38 - j6.43$           | $1.30 - j2.46$         |
| 1845       | P1dB | $3.70 - j7.13$           | $1.40 - j2.51$         |
| 1880       | P1dB | $4.23 - j7.74$           | $1.27 - j2.55$         |

Figure 12. Pulsed CW Output Power  
versus Input Power @ 30 V

NOTE: Measurement made on the Class AB, carrier side of the device.

# PACKAGE DIMENSIONS



|                                                         |  |                          |                            |
|---------------------------------------------------------|--|--------------------------|----------------------------|
| © FREESCALE SEMICONDUCTOR, INC.<br>ALL RIGHTS RESERVED. |  | MECHANICAL OUTLINE       | PRINT VERSION NOT TO SCALE |
| TITLE:<br><br>NI-1230-8                                 |  | DOCUMENT NO: 98ASA00120D | REV: C                     |
|                                                         |  | CASE NUMBER: 375I-04     | 18 JUL 2011                |
|                                                         |  | STANDARD: NON-JEDEC      |                            |

MRF8P18265HR6 MRF8P18265HSR6

NOTES:


1.0 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M–1994.

2.0 CONTROLLING DIMENSION: INCH

3.0 DIMENSION H1 AND H2 ARE MEASURED .030 (0.762) AWAY FROM PACKAGE BODY.  
H1 APPLIES TO PINS 2,3,6,7. H2 APPLIES TO PINS 1,4,5,8.

4.0 RECOMMENDED BOLT CENTER DIMENSION OF 1.52 (38.61) BASED ON M3 SCREW.

| DIM                                                     | INCH      |       | MILLIMETER         |       | DIM                      | INCH                       |       | MILLIMETER |             |
|---------------------------------------------------------|-----------|-------|--------------------|-------|--------------------------|----------------------------|-------|------------|-------------|
|                                                         | MIN       | MAX   | MIN                | MAX   |                          | MIN                        | MAX   | MIN        | MAX         |
| A                                                       | 1.615     | 1.625 | 41.02              | 41.28 | N                        | 1.218                      | 1.242 | 30.94      | 31.55       |
| B                                                       | .395      | .405  | 10.03              | 10.29 | Q                        | .120                       | .130  | 3.05       | 3.3         |
| C                                                       | .150      | .200  | 3.81               | 5.08  | R                        | .365                       | .375  | 9.27       | 9.53        |
| D                                                       | .455      | .465  | 11.56              | 11.81 | S                        | .365                       | .375  | 9.27       | 9.53        |
| E                                                       | .062      | .066  | 1.57               | 1.68  | V1                       | 1.320                      | 1.330 | 33.53      | 33.78       |
| F                                                       | .004      | .007  | 0.10               | 0.18  | U                        | .035                       | .045  | 0.89       | 1.14        |
| G                                                       | 1.400 BSC |       | 35.56 BSC          |       | W1                       | .225                       | .235  | 5.72       | 5.97        |
| H1                                                      | .082      | .090  | 2.08               | 2.29  | W2                       | .431                       | .441  | 10.95      | 11.20       |
| H2                                                      | .078      | .094  | 1.98               | 2.39  | W3                       | .491                       | .501  | 12.47      | 12.73       |
| K                                                       | .117      | .137  | 2.97               | 3.48  | Y                        | 1.390 BSC                  |       | 35.31 BSC  |             |
| L                                                       | .540 BSC  |       | 13.72 BSC          |       | Z                        | ---                        | R.020 | ---        | R0.51       |
| M                                                       | 1.219     | 1.241 | 30.96              | 31.52 | aaa                      | .013                       |       | 0.33       |             |
|                                                         |           |       |                    |       | bbb                      | .010                       |       | 0.25       |             |
|                                                         |           |       |                    |       | ccc                      | .020                       |       | 0.51       |             |
| © FREESCALE SEMICONDUCTOR, INC.<br>ALL RIGHTS RESERVED. |           |       | MECHANICAL OUTLINE |       |                          | PRINT VERSION NOT TO SCALE |       |            |             |
| TITLE:<br><br>NI-1230-8                                 |           |       |                    |       | DOCUMENT NO: 98ASA00120D |                            |       |            | REV: C      |
|                                                         |           |       |                    |       | CASE NUMBER: 375I-04     |                            |       |            | 18 JUL 2011 |
|                                                         |           |       |                    |       | STANDARD: NON-JEDEC      |                            |       |            |             |



|                                                         |                          |                    |                            |
|---------------------------------------------------------|--------------------------|--------------------|----------------------------|
| © FREESCALE SEMICONDUCTOR, INC.<br>ALL RIGHTS RESERVED. |                          | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE |
| TITLE:<br><br>NI-1230S-8                                | DOCUMENT NO: 98ASA00155D |                    | REV: B                     |
|                                                         | CASE NUMBER: 375J-03     |                    | 18 JUL 2011                |
|                                                         | STANDARD: NON-JEDEC      |                    |                            |

NOTES:

1.0 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M–1994.

2.0 CONTROLLING DIMENSION: INCH

3.0 DIMENSION H1 AND H2 ARE MEASURED .030 (0.762) AWAY FROM PACKAGE BODY.  
H1 APPLIES TO PINS 2,3,6,7. H2 APPLIES TO PINS 1,4,5,8.

4.0 –DELETED–

| DIM                                                     | INCH     |       | MILLIMETER         |       | DIM                      | INCH                       |       | MILLIMETER |             |
|---------------------------------------------------------|----------|-------|--------------------|-------|--------------------------|----------------------------|-------|------------|-------------|
|                                                         | MIN      | MAX   | MIN                | MAX   |                          | MIN                        | MAX   | MIN        | MAX         |
| A                                                       | 1.265    | 1.275 | 32.13              | 32.39 | N                        | 1.218                      | 1.242 | 30.94      | 31.55       |
| B                                                       | .395     | .405  | 10.03              | 10.29 | R                        | .365                       | .375  | 9.27       | 9.53        |
| C                                                       | .150     | .200  | 3.81               | 5.08  | S                        | .365                       | .375  | 9.27       | 9.53        |
| D                                                       | .455     | .465  | 11.56              | 11.81 | U                        | .035                       | .045  | 0.89       | 1.14        |
| E                                                       | .062     | .066  | 1.57               | 1.68  | V1                       | 1.320                      | 1.330 | 33.53      | 33.78       |
| F                                                       | .004     | .007  | 0.10               | 0.18  | T3                       | DELETED                    |       | DELETED    |             |
| H1                                                      | .082     | .090  | 2.08               | 2.29  | W1                       | .225                       | .235  | 5.72       | 5.97        |
| H2                                                      | .078     | .094  | 1.98               | 2.39  | W2                       | .431                       | .441  | 10.95      | 10.20       |
| K                                                       | .117     | .137  | 2.97               | 3.48  | W3                       | .491                       | .501  | 12.47      | 12.73       |
| L                                                       | .540 BSC |       | 13.72 BSC          |       | Y                        | 1.390 BSC                  |       | 35.31 BSC  |             |
| M                                                       | 1.219    | 1.241 | 30.96              | 31.52 | Z                        | ---                        | R.040 | ---        | R1.02       |
|                                                         |          |       |                    |       | aaa                      | .005                       |       | 0.13       |             |
|                                                         |          |       |                    |       | bbb                      | .010                       |       | 0.25       |             |
|                                                         |          |       |                    |       | ccc                      | .020                       |       | 0.51       |             |
| © FREESCALE SEMICONDUCTOR, INC.<br>ALL RIGHTS RESERVED. |          |       | MECHANICAL OUTLINE |       |                          | PRINT VERSION NOT TO SCALE |       |            |             |
| TITLE:<br><br>NI-1230S-8                                |          |       |                    |       | DOCUMENT NO: 98ASA00155D |                            |       |            | REV: B      |
|                                                         |          |       |                    |       | CASE NUMBER: 375J-03     |                            |       |            | 18 JUL 2011 |
|                                                         |          |       |                    |       | STANDARD: NON-JEDEC      |                            |       |            |             |

## PRODUCT DOCUMENTATION AND SOFTWARE

Refer to the following documents and software to aid your design process.

### Application Notes

- AN1955: Thermal Measurement Methodology of RF Power Amplifiers

### Engineering Bulletins

- EB212: Using Data Sheet Impedances for RF LDMOS Devices

### Software

- Electromigration MTTF Calculator
- RF High Power Model
- .s2p File

For Software, do a Part Number search at <http://www.freescale.com>, and select the “Part Number” link. Go to the Software & Tools tab on the part’s Product Summary page to download the respective tool.

## REVISION HISTORY

The following table summarizes revisions to this document.

| Revision | Date      | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|----------|-----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 0        | Aug. 2010 | <ul style="list-style-type: none"><li>• Initial Release of Data Sheet</li></ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| 1        | Feb. 2012 | <ul style="list-style-type: none"><li>• Table 3, ESD Protection Characteristics, removed the word “Minimum” after the ESD class rating. ESD ratings are characterized during new product development but are not 100% tested during production. ESD ratings provided in the data sheet are intended to be used as a guideline when handling ESD sensitive devices, p. 2</li><li>• Removed Fig. 5, Possible Circuit Topologies, and renumbered all subsequent figures, p. 5–8</li><li>• Replaced Case Outline 375I-03, Issue B with 375I-04, Issue C, p. 1, 9, 10. On Sheet 2, changed dimension F in mm from 0.1–0.18 to 0.10–0.18, changed dimension U in mm from 0.89–1.02 to 0.89–1.14, changed dimension W3 in mm from 12.47–12.72 to 12.47–12.73.</li><li>• Replaced Case Outline 375J-02, Issue A with 375J-03, Issue B, p. 1, 11, 12. On Sheet 2, changed dimension A in mm from 32.13–32.38 to 32.13–32.39, changed dimension F in mm from 0.1–0.18 to 0.10–0.18, changed dimension U in mm from 8.89–11.43 to 0.89–1.14.</li></ul> |

## ***How to Reach Us:***

### **Home Page:**

[www.freescale.com](http://www.freescale.com)

### **Web Support:**

<http://www.freescale.com/support>

### **USA/Europe or Locations Not Listed:**

Freescale Semiconductor, Inc.  
Technical Information Center, EL516  
2100 East Elliot Road  
Tempe, Arizona 85284  
1-800-521-6274 or +1-480-768-2130  
[www.freescale.com/support](http://www.freescale.com/support)

### **Europe, Middle East, and Africa:**

Freescale Halbleiter Deutschland GmbH  
Technical Information Center  
Schatzbogen 7  
81829 Muenchen, Germany  
+44 1296 380 456 (English)  
+46 8 52200080 (English)  
+49 89 92103 559 (German)  
+33 1 69 35 48 48 (French)  
[www.freescale.com/support](http://www.freescale.com/support)

### **Japan:**

Freescale Semiconductor Japan Ltd.  
Headquarters  
ARCO Tower 15F  
1-8-1, Shimo-Meguro, Meguro-ku,  
Tokyo 153-0064  
Japan  
0120 191014 or +81 3 5437 9125  
[support.japan@freescale.com](mailto:support.japan@freescale.com)

### **Asia/Pacific:**

Freescale Semiconductor China Ltd.  
Exchange Building 23F  
No. 118 Jianguo Road  
Chaoyang District  
Beijing 100022  
China  
+86 10 5879 8000  
[support.asia@freescale.com](mailto:support.asia@freescale.com)

### **For Literature Requests Only:**

Freescale Semiconductor Literature Distribution Center  
1-800-441-2447 or +1-303-675-2140  
Fax: +1-303-675-2150  
[LDCForFreescaleSemiconductor@hibbertgroup.com](mailto:LDCForFreescaleSemiconductor@hibbertgroup.com)

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale™ and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners.

© Freescale Semiconductor, Inc. 2010, 2012. All rights reserved.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Freescale Semiconductor:

[MRF8P18265HR6](#) [MRF8P18265HSR5](#) [MRF8P18265HSR6](#)