



+ WIRE AND CABLE

MULTICORE CABLE



✓ Active

TE CONNECTIVITY (TE)

**55PC1221-20-4/5-9**

Raychem | RC , SP

CA1718-000

TE Internal Number: CA1718-000

Alias ID: 7-1899101-5

EU RoHS Compliant

EU ELV Compliant

Cable Type Spec 55

Conductor Diameter .99 mm [.039 in]

Number of Strands 19

Strand Size (AWG) 32

Overall Outside Diameter 3.66 mm [.144 in]

**PRODUCT DRAWING**

English

**DOCUMENTATION**

Product Drawings

**TWO CONDUCTOR CABLE, SHIELDED, JACKETED, GENERAL PURPOSE, 600 VOLT**

PDF

English

Product Specifications

Product Specification

**Process-Controlled Wire And Cable, Radiation-Crosslinked, Modified ETFE-Insulated**

PDF

English

**FEATURES**



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

#### Product Type Features

**Cable Type** Spec 55

**Shielded** Yes

**Cable Style** Jacketed, Round Braided

**Product Type** Cable

**Product Classification** Cable - High Performance - Spec 44, 55 & RCW

---

#### Configuration Features

**Number of Strands** 19

**Number of Conductors** 2

---

#### Electrical Characteristics

**Voltage Rating (V)** 600

---

#### Body Features

**Shield Material** Tin-Plated Copper

**Insulation Material** Radiation-Crosslinked, Modified ETFE

**Jacket Color** White

**Wire Color** Green, Yellow

**Conductor Material** Tin-Plated Copper

---

#### Dimensions

**Conductor Diameter** .99 mm [.039 in]

**Strand Size (AWG)** 32

**Overall Outside Diameter** 3.66 mm [.144 in]

**Wire Size (AWG)** 20

**Wire Diameter** 1.42 mm [.056 in]

---

#### Usage Conditions

**Operating Temperature Range (°C)** -65 – 150

---

#### Other

**Wire Source** United Kingdom, United States

---

### PRODUCT COMPLIANCE



#### Statement of Compliance

### Statement of Compliance

PDF

