





PRODUCT NO.
SEE TABLE



mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		FCI		www.fciconnect.com	
lir	ecn no	dr	date	linear	angular	dr	date	projection	title	product family	MOD JACK	code	
A	V80489	BWN	4/6/98						RJ45 ENHANCED SHIELD	PORT ASSY SNAP PEG	MOD JACK	code	213
B	V81781	RGD	10/9/98										
C	V90568	RGD	2/23/99										
D	V12591	LP	3/19/02										
E	V03-1103	PJ	10/17/03										
F	M05-0066	MHT	4/15/05										
revision				oppd	B.MARSHALL	2/11/98		scale	A	74453		sheet	1 of 4
sheet index				1	2	3	4						


NOTE: PLEASE CHECK FOR AVAILABILITY, NOT ALL OPTIONS AVAILABLE.

PRODUCT NO	DIM A	DIM C	DIM F
74453-001XLF	3.05 [0.120]	N/A	1.02[0.040]
74453-002XLF	4.57 [0.179]	N/A	1.27[0.050]
74453-003XLF	N/A	3.05[0.120]	1.27[0.050]

SHIELD OPTION X	DESCRIPTION
1	SPRINGS ON TOP, BOTTOM AND SIDES
2	NO SPRINGS
3	SPRINGS ON TOP AND BOTTOM ONLY
4	SPRINGS ON TOP, BOTTOM AND 1 PER SIDE, STAGGERED
5	SAME AS OPTION 4 EXCEPT OPPOSITE STAGGER

NOTES:

1. RECOMMENDED PCB THICKNESS 1.57 [0.062].
2. HOUSING MAT'L: HIGH TEMP. THERMOPLASTIC, COLOR BLACK, UL94V-0.
3. CONTACT MAT'L: COPPER ALLOY
MATING AREA PLATING: 1.27µm/50µ" MIN Au OVER Ni.
SOLDER AREA PLATING: 2.54µm/100µ" MIN TIN LEAD OVER Ni.
4. SHIELDING MAT'L: TIN PLATED COPPER ALLOY.
5. ALL DIMENSIONS IN MILLIMETERS AND INCHES.
6. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M 1994.
7. COMPANY LOGO LOCATED IN THIS AREA.
8. PART NUMBERS WITH LF IN THE END ARE LEAD FREE.
9. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AN OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
10. THE HOUSING TEMPERATURE WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5 MM MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.




mat'l. code			tolerances unless otherwise specified		CUSTOMER COPY		FCI	
lfr	ecn no	dr	date		linear	projection	title	
F					$\pm .01$	$\pm .005$	RJ45 ENHANCED SHIELD	
					$\pm .005$	$\pm .0020$	PORT ASSY SNAP PEG	
					angles	$G \pm .2$	product family	MOD JACK
					dr	R.GRAPE 2/11/98	size	213
					engr	B.MARSHALL 2/11/98	code	213
					chr	B.MARSHALL 2/11/98	sheet	4 of 4
					oppl	B.MARSHALL 2/11/98	scale	1:1
							part no	74453
sheet	revision	sheet						
index								

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de C.F.I. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NO.
SEE TABLE




Tous droits strictement réservés. Reproduction ou communication à des tiers
interdite sans que la forme que ce soit sans autorisation écrite du propriétaire.
Property of FCI. Copyright FCI. Droits de reproduction FCI.



(APPLIES TO -001XLF)
RECOMMENDED P.C.B. LAYOUT
AS VIEWED FROM TOP SIDE (COMPONENT SIDE)



(APPLIES TO -002XLF)
RECOMMENDED P.C.B. LAYOUT
AS VIEWED FROM TOP SIDE (COMPONENT SIDE)



(APPLIES TO -003XLF)
RECOMMENDED P.C.B. LAYOUT
AS VIEWED FROM TOP SIDE (COMPONENT SIDE)

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecp no	dr	date	linear	projection	title	www.fci.com
F				XX±.13/XXX ±.005	Ø	RJ45 ENHANCED SHIELD	
				XXX±.051/XXX ±.0020		PORT ASSY SNAP PEG	
				angles	Ø ±.2°	product family	MOD JACK
				dr	R.GRAPE 2/11/98	size	21.3
				encl	B.MARSHALL 2/11/98	code	21.3
				chr	B.MARSHALL 2/11/98	sheet	3 of 4
				appd	B.MARSHALL 2/11/98	scale	1:1
sheet	revision	sheet	sheet	sheet	sheet	A	74453
index	index	index	index	index	index	index	index



Property of FCI. Copyright FCI.

PRODUCT NO.	SEE TABLE
-------------	-----------

