



High Isolation Power Transformers

PA3964.XXXNL and PA3965.XXXNL - SMT



- Power Range:** up to 10W
- Height:** 7.0mm to 14.0mm Max
- Footprint:** 18.0mm x 15.6mm Max
- Topology:** Forward, Flyback and Push-pull
- Isolation:** 5.0kVrms (1000Vrms continuous)
- Insulation:** Basic, 12mm creepage and clearance distance
- Patent Pending:**

Electrical Specifications @ 25°C - Operating Temperature -40°C to +130°C

PA3964.001NL	Pri. Inductance	(1-2)	15.6mH $\pm 15\%$	ACTIVE CLAMP FORWARD TRANSFORMER
	Lk. Inductance	(1-2) with (3, 4, 5, 8) shorted	1.4 μ H MAX	
	DCR	(1-2)	1000m Ω MAX	
		(3-4)	570m Ω MAX	
		(5-8)	450m Ω MAX	
	Hi-Pot	Pri-Sec	5000Vrms	
PA3964.002NL	Pri. Inductance	(3-4)	0.51mH $\pm 15\%$	PUSH-PULL TRANSFORMER
	Lk. Inductance	(5-8) with (6,7) and (1,2,3,4) shorted	1.4 μ H MAX	
	DCR	(5-6)=(7-8)	115m Ω MAX	
		(1-2)=(3-4)	162m Ω MAX	
	Hi-Pot	Pri-Sec	5000Vrms	
PA3965.001NL	Pri. Inductance	(1-2)	680 μ H $\pm 15\%$	DCM FLYBACK TRANSFORMER
		(1-2)	544 μ H Min @ 0.7A	
	Lk. Inductance	(1-2) with (3,4,5,8) shorted	15 μ H MAX	
	DCR	(1-2)	1870m Ω MAX	
		(3-4)	290m Ω MAX	
		(5-8)	90m Ω MAX	
	Hi-Pot	Pri-Sec	5000Vrms	
PA3965.002NL	Pri. Inductance	(1-2)	680 μ H $\pm 15\%$	DCM FLYBACK TRANSFORMER
		(1-2)	544 μ H Min @ 0.7A	
	Lk. Inductance	(1-2) with (3,4,5,8) shorted	15 μ H MAX	
	DCR	(1-2)	1870m Ω MAX	
		(3-4)	290m Ω MAX	
		(5-8)	25m Ω MAX	
	Hi-Pot	Pri-Sec	5000Vrms	

USA 858 674 8100

Germany 49 2354 777 100

Singapore 65 6287 8998

Shanghai 86 21 62787060

China 86 755 33966678

Taiwan 886 3 4356768

High Isolation Power Transformers


PA3964.XXXNL and PA3965.XXXNL - SMT

Notes:

1. The temperature of the component (ambient plus temperature rise) must be within the stated operating temperature range.
2. Continuous isolation voltage confirmed by 125°C/1000hrs accelerated aging with the bias voltage applied between primary and secondary windings.
3. Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the part number (i.e. (PA3964.001NL becomes PA3964.001NLT). Pulse complies with industry standard tape and reel specification EIA481. The tape and reel for this product has a width (W=32mm), pitch (Po=24mm) and depth (Ko) is equal to 8.0 for PA3964.XXXNLT and 14.5 for PA3965.XXXNLT. PA3964.XXXNLT has 300pcs per reel. PA3965.XXXNLT has 150pcs per reel.
4. US Patent application number: 13/291,545

Mechanicals

PA3964.XXXNL and PA3965.XXXNL



For More Information

Pulse Worldwide Headquarters

15255 Innovation Drive Ste 100
San Diego, CA 92128
U.S.A.

Tel: 858 674 8100
Fax: 858 674 8262

Pulse Europe

Pulse Electronics GmbH
Am Rottland 12
58540 Meinerzhagen
Germany

Tel: 49 2354 777 100
Fax: 49 2354 777 168

Pulse China Headquarters

B402, Shenzhen Academy of
Aerospace Technology Bldg.
10th Kejinan Road
High-Tech Zone
Nanshan District
Shenzhen, PR China 518057

Tel: 86 755 33966678
Fax: 86 755 33966700

Pulse North China

Room 2704/2705
Super Ocean Finance Ctr.
2067 Yan An Road West
Shanghai 200336
China

Tel: 86 21 62787060
Fax: 86 2162786973

Pulse South Asia

135 Joo Seng Road
#03-02
PM Industrial Bldg.
Singapore 368363

Tel: 65 6287 8998
Fax: 65 6287 8998

Pulse North Asia

3F, No. 198
Zhongyuan Road
Zhongli City
Taoyuan County 320
Taiwan R. O. C.

Tel: 886 3 4356768
Fax: 886 3 4356823 (Pulse)
Fax: 886 3 4356820 (FRE)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2017. Pulse Electronics, Inc. All rights reserved.