



## Features

- RoHS compliant\*
- Values from 0.02 to 9.10 ohms
- Tolerance of 1 % or 5 %
- Five package sizes available
- Tape and reel packaging



Select models are currently available, but not recommended for new designs. See [Product Obsolescence Memo](#) for details.

## CRL Series - Low Value Chip Resistors

### Electrical Characteristics

| Characteristic                                                            | Model CRL0603                             | Model CRL0805                    | Model CRL1206                    | Model CRL2010                    | Model CRL2512                    |
|---------------------------------------------------------------------------|-------------------------------------------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|
| Power Rating @ 70 °C                                                      | 0.100 watt                                | 0.125 watt                       | 0.250 watt                       | 0.50 watt                        | 1.00 watt                        |
| Operating Temperature Range                                               | -55 to +125 °C                            |                                  |                                  |                                  |                                  |
| Derated to Zero Load at                                                   | +125 °C                                   |                                  |                                  |                                  |                                  |
| Maximum Working Voltage                                                   | (PR) <sup>1/2</sup>                       | (PR) <sup>1/2</sup>              | (PR) <sup>1/2</sup>              | (PR) <sup>1/2</sup>              | (PR) <sup>1/2</sup>              |
| Resistance Range<br>E24 Values:<br>See Value Table:                       | 0.10 to 9.10 Ω<br>N/A                     | 0.10 to 9.10 Ω<br>0.05 to 0.09 Ω | 0.10 to 9.10 Ω<br>0.02 to 0.09 Ω | 0.10 to 9.10 Ω<br>0.02 to 0.09 Ω | 0.10 to 9.10 Ω<br>0.02 to 0.09 Ω |
| Temperature Coefficient<br>0.05 Ω to 9.10 Ω<br>0.03 Ω to 0.04 Ω<br>0.02 Ω | ±200 PPM/°C<br>±400 PPM/°C<br>±600 PPM/°C |                                  |                                  |                                  |                                  |

### Value Table

| Value (Ω) | CRL0603<br>1 % | CRL0603<br>5 % | CRL0805<br>1 % | CRL0805<br>5 % | CRL1206<br>1 % | CRL1206<br>5 % | CRL2010<br>1 % | CRL2010<br>5 % | CRL2512<br>1 % | CRL2512<br>5 % |
|-----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| 0.02      | Not Available  | Not Available  | Not Available  | Not Available  | A              | A              | P              | P              | P              | P              |
| 0.03      | Not Available  | Not Available  | Not Available  | Not Available  | A              | A              | P              | P              | P              | P              |
| 0.04      | Not Available  | Not Available  | Not Available  | Not Available  | A              | A              | P              | P              | P              | P              |
| 0.05      | Not Available  | Not Available  | A              | A              | A              | A              | P              | P              | P              | P              |
| 0.06      | Not Available  | Not Available  | A              | A              | A              | A              | A              | A              | A              | A              |
| 0.07      | Not Available  | Not Available  | A              | A              | A              | A              | A              | A              | A              | A              |
| 0.08      | Not Available  | Not Available  | A              | A              | A              | A              | A              | A              | A              | A              |
| 0.09      | Not Available  | Not Available  | A              | A              | A              | A              | A              | A              | A              | A              |

P = Popular Value

A = Available Value (may have greater minimum order quantity)

### Environmental Characteristics

| Description                  | Method                                                                                 | Limit                                                                                                                |
|------------------------------|----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------|
| Short Time Overload          | 2.5 x (PR) <sup>1/2</sup> for 5 seconds.<br>(IEC 115-1 4.13)                           | 1 % Tolerance: $\Delta R \leq \pm(1 \% + 0.001 \Omega)$<br>5 % Tolerance: $\Delta R \leq \pm(2 \% + 0.001 \Omega)$   |
| Load Life                    | (PR) <sup>1/2</sup> for 1000 hours; 1.5 hours on; 0.5 hours off.<br>(IEC 115-1 4.25.1) | 1 % Tolerance: $\Delta R \leq \pm(1 \% + 0.001 \Omega)$<br>5 % Tolerance: $\Delta R \leq \pm(2 \% + 0.001 \Omega)$   |
| Resistance to Soldering Heat | 260 °C for 10 seconds.<br>(IEC 115-1 4.18)                                             | 1 % Tolerance: $\Delta R \leq \pm(0.5 \% + 0.001 \Omega)$<br>5 % Tolerance: $\Delta R \leq \pm(1 \% + 0.001 \Omega)$ |
| Thermal Shock                | 5 cycles from -55 °C to +125 °C, 30 minutes at temperature.<br>(IEC 115-1 4.19)        | 1 % Tolerance: $\Delta R \leq \pm(0.5 \% + 0.001 \Omega)$<br>5 % Tolerance: $\Delta R \leq \pm(1 \% + 0.001 \Omega)$ |

\*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.


# CRL Series - Low Value Chip Resistors

**BOURNS®**

## Chip Dimensions


| Dimension | Model CRL0603                             | Model CRL0805                             | Model CRL1206                             | Model CRL2010                             | Model CRL2512                             |
|-----------|-------------------------------------------|-------------------------------------------|-------------------------------------------|-------------------------------------------|-------------------------------------------|
| L         | $\frac{1.60 \pm 0.10}{(0.063 \pm 0.004)}$ | $\frac{2.00 \pm 0.15}{(0.079 \pm 0.006)}$ | $\frac{3.20 \pm 0.15}{(0.126 \pm 0.006)}$ | $\frac{5.00 \pm 0.20}{(0.197 \pm 0.008)}$ | $\frac{6.30 \pm 0.20}{(0.248 \pm 0.008)}$ |
| W         | $\frac{0.80 \pm 0.10}{(0.031 \pm 0.004)}$ | $\frac{1.25 \pm 0.10}{(0.049 \pm 0.004)}$ | $\frac{1.60 \pm 0.15}{(0.063 \pm 0.006)}$ | $\frac{2.50 \pm 0.20}{(0.098 \pm 0.008)}$ | $\frac{3.10 \pm 0.20}{(0.122 \pm 0.008)}$ |
| H         | $\frac{0.45 \pm 0.10}{(0.018 \pm 0.004)}$ | $\frac{0.50 \pm 0.10}{(0.020 \pm 0.004)}$ | $\frac{0.60 \pm 0.10}{(0.024 \pm 0.004)}$ | $\frac{0.60 \pm 0.10}{(0.024 \pm 0.004)}$ | $\frac{0.60 \pm 0.10}{(0.024 \pm 0.004)}$ |
| $l_1$     | $\frac{0.30 \pm 0.20}{(0.012 \pm 0.008)}$ | $\frac{0.40 \pm 0.20}{(0.016 \pm 0.008)}$ | $\frac{0.50 \pm 0.25}{(0.020 \pm 0.010)}$ | $\frac{0.60 \pm 0.25}{(0.024 \pm 0.010)}$ | $\frac{0.60 \pm 0.25}{(0.024 \pm 0.010)}$ |
| $l_2$     | $\frac{0.30 \pm 0.20}{(0.012 \pm 0.008)}$ | $\frac{0.40 \pm 0.20}{(0.016 \pm 0.008)}$ | $\frac{0.50 \pm 0.25}{(0.020 \pm 0.010)}$ | $\frac{0.60 \pm 0.25}{(0.024 \pm 0.010)}$ | $\frac{0.60 \pm 0.20}{(0.024 \pm 0.008)}$ |

## Dimensional Drawing



DIMENSIONS:  $\frac{\text{MM}}{(\text{INCHES})}$

## Derating Curve



## How to Order

**CRL 0603 - F W - R090 E LF**

Model \_\_\_\_\_  
(CRL = Chip Resistor Low Value)

Size \_\_\_\_\_  
• 0603  
• 0805  
• 1206  
• 2010  
• 2512

Resistance Tolerance \_\_\_\_\_  
F =  $\pm 1\%$   
J =  $\pm 5\%$

TCR (PPM/°C) \_\_\_\_\_  
W =  $\pm 200$  (0.05 to 9.10  $\Omega$ )  
V =  $\pm 400$  (0.03 to 0.04  $\Omega$ )  
U =  $\pm 600$  (0.02  $\Omega$ )

Resistance Value (1 % or 5 %) \_\_\_\_\_  
• R stands for decimal point. Three significant digits: (R090 = 0.09  $\Omega$ ; 9R10 = 9.10  $\Omega$ )

Packaging \_\_\_\_\_  
• CRL0603, CRL0805, CRL1206: E = Paper Tape, Plastic Reel, 5,000 pcs.  
• CRL2010, CRL2512: E = Embossed Plastic Tape, Plastic Reel, 4,000 pcs.

Termination \_\_\_\_\_  
LF = Tin-plated (RoHS compliant)

# CRL Series - Low Value Chip Resistors


**BOURNS®**

## Packaging Dimensions - Tape

| Dimension      | Model CRL0603                             | Model CRL0805                                          | Model CRL1206                                          | Model CRL2010                             | Model CRL2512                              |
|----------------|-------------------------------------------|--------------------------------------------------------|--------------------------------------------------------|-------------------------------------------|--------------------------------------------|
| A              | $\frac{1.10 \pm 0.10}{(0.043 \pm 0.004)}$ | $\frac{1.65 + 0.20 / - 0.10}{(0.065 + 0.008 / -.004)}$ | $\frac{1.95 + 0.10 / - 0.05}{(0.077 + 0.004 / -.002)}$ | $\frac{2.80 \pm 0.20}{(0.110 \pm 0.008)}$ | $\frac{3.50 \pm 0.20}{(0.138 \pm 0.008)}$  |
| B              | $\frac{1.90 \pm 0.10}{(0.075 \pm 0.004)}$ | $\frac{2.40 + 0.20 / - 0.10}{(0.094 + 0.008 / -.004)}$ | $\frac{3.50 \pm 0.10}{(0.138 \pm 0.004)}$              | $\frac{5.50 \pm 0.20}{(0.217 \pm 0.008)}$ | $\frac{6.70 \pm 0.20}{(0.264 \pm 0.008)}$  |
| W              | $\frac{8.00 \pm 0.20}{(0.315 \pm 0.008)}$ | $\frac{8.00 \pm 0.20}{(0.315 \pm 0.008)}$              | $\frac{8.00 \pm 0.20}{(0.315 \pm 0.008)}$              | $\frac{12.0 \pm 0.30}{(0.472 \pm 0.012)}$ | $\frac{12.00 \pm 0.30}{(0.472 \pm 0.012)}$ |
| F              | $\frac{3.50 \pm 0.05}{(0.138 \pm 0.002)}$ | $\frac{3.50 \pm 0.05}{(0.138 \pm 0.002)}$              | $\frac{3.50 \pm 0.05}{(0.138 \pm 0.002)}$              | $\frac{5.50 \pm 0.05}{(0.217 \pm 0.002)}$ | $\frac{5.50 \pm 0.05}{(0.217 \pm 0.002)}$  |
| P <sub>0</sub> | $\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$ | $\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$              | $\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$              | $\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$ | $\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$  |

## Packaging Dimensions - Reel

| Dimension | Model CRL0603                              | Model CRL0805                              | Model CRL1206                              | Model CRL2010                              | Model CRL2512                              |
|-----------|--------------------------------------------|--------------------------------------------|--------------------------------------------|--------------------------------------------|--------------------------------------------|
| N         | $\frac{80.00 \pm 1.00}{(3.150 \pm 0.040)}$ | $\frac{80.00 \pm 1.00}{(3.150 \pm 0.040)}$ | $\frac{80.00 \pm 1.00}{(3.150 \pm 0.040)}$ | $\frac{80.00 \pm 0.20}{(3.150 \pm 0.008)}$ | $\frac{80.00 \pm 0.20}{(3.150 \pm 0.008)}$ |
| D         | $\frac{20.50}{(0.807)}$                    | $\frac{20.50}{(0.807)}$                    | $\frac{20.50}{(0.807)}$                    | $\frac{20.00}{(0.787)}$ MIN.               | $\frac{20.00}{(0.787)}$ MIN.               |
| T         | $\frac{10.00 \pm 1.50}{(0.394 \pm 0.059)}$ | $\frac{10.00 \pm 1.50}{(0.394 \pm 0.059)}$ | $\frac{10.00 \pm 1.50}{(0.394 \pm 0.059)}$ | $\frac{16.70}{(0.657)}$ MAX.               | $\frac{16.70}{(0.657)}$ MAX.               |



REV. 08/15

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Bourns:

|                                  |                                  |                                  |                                  |                                  |
|----------------------------------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|
| <a href="#">CRL2512-FU-R016E</a> | <a href="#">CRL2512-JU-R016E</a> | <a href="#">CRL0805-JW-R620E</a> | <a href="#">CRL0805-FW-R620E</a> | <a href="#">CRL2512-JU-R015E</a> |
| <a href="#">CRL2512-FU-R015E</a> | <a href="#">CRL0603-JW-R100E</a> | <a href="#">CRL2512-JU-R011E</a> | <a href="#">CRL2010-FW-R560E</a> | <a href="#">CRL2512-JU-R018E</a> |
| <a href="#">CRL2010-JW-R560E</a> | <a href="#">CRL2512-FU-R018E</a> | <a href="#">CRL2512-FU-R010E</a> | <a href="#">CRL2512-JU-R013E</a> | <a href="#">CRL0603-FW-R100E</a> |
| <a href="#">CRL2512-FU-R011E</a> | <a href="#">CRL2512-FU-R013E</a> | <a href="#">CRL2512-JU-R010E</a> | <a href="#">CRL2512-JU-R012E</a> | <a href="#">CRL2512-FW-R051E</a> |
| <a href="#">CRL2512-FU-R012E</a> | <a href="#">CRL2512-JW-R056E</a> | <a href="#">CRL2512-FW-R056E</a> | <a href="#">CRL2512-JW-R051E</a> | <a href="#">CRL0603-FW-R180E</a> |
| <a href="#">CRL2512-FW-R091E</a> | <a href="#">CRL0603-JW-R180E</a> | <a href="#">CRL2512-JW-R091E</a> | <a href="#">CRL0805-JW-R051E</a> | <a href="#">CRL2010-FW-R220E</a> |
| <a href="#">CRL2010-JW-R220E</a> | <a href="#">CRL2010-FW-R068E</a> | <a href="#">CRL0805-FW-R056E</a> | <a href="#">CRL2512-JW-R560E</a> | <a href="#">CRL0805-JW-R056E</a> |
| <a href="#">CRL0805-FW-R051E</a> | <a href="#">CRL2512-FW-R560E</a> | <a href="#">CRL0603-JW-R560E</a> | <a href="#">CRL1206-FW-R075E</a> | <a href="#">CRL1206-JW-R075E</a> |
| <a href="#">CRL0603-FW-R560E</a> | <a href="#">CRL1206-FW-R051E</a> | <a href="#">CRL1206-JW-R051E</a> | <a href="#">CRL0603-JW-R910E</a> | <a href="#">CRL0603-FW-R910E</a> |
| <a href="#">CRL1206-FW-R220E</a> | <a href="#">CRL1206-JW-R220E</a> | <a href="#">CRL1206-JV-R027E</a> | <a href="#">CRL2010-FU-R013E</a> | <a href="#">CRL1206-FV-R024E</a> |
| <a href="#">CRL1206-JV-R024E</a> | <a href="#">CRL1206-FV-R027E</a> | <a href="#">CRL2512-FW-R470E</a> | <a href="#">CRL2512-JW-R470E</a> | <a href="#">CRL2010-FU-R015E</a> |
| <a href="#">CRL1206-FU-R020E</a> | <a href="#">CRL1206-JU-R020E</a> | <a href="#">CRL0805-JV-R047E</a> | <a href="#">CRL0805-FW-R200E</a> | <a href="#">CRL0805-JW-R200E</a> |
| <a href="#">CRL1206-FV-R022E</a> | <a href="#">CRL1206-JV-R022E</a> | <a href="#">CRL0805-FV-R047E</a> | <a href="#">CRL1206-FW-R430E</a> | <a href="#">CRL2010-JW-R180E</a> |
| <a href="#">CRL1206-JW-R430E</a> | <a href="#">CRL2010-FW-R180E</a> | <a href="#">CRL1206-FW-R330E</a> | <a href="#">CRL2010-FW-R120E</a> | <a href="#">CRL2010-JW-R120E</a> |
| <a href="#">CRL2010-JW-R240E</a> | <a href="#">CRL2010-FW-R240E</a> | <a href="#">CRL1206-JW-R330E</a> | <a href="#">CRL0805-FW-R390E</a> | <a href="#">CRL0603-JW-R620E</a> |
| <a href="#">CRL0603-FW-R620E</a> | <a href="#">CRL0805-JW-R390E</a> | <a href="#">CRL1206-FW-R200E</a> | <a href="#">CRL1206-JW-R200E</a> | <a href="#">CRL0805-FW-R430E</a> |
| <a href="#">CRL0805-JW-R430E</a> | <a href="#">CRL2512-FV-R024E</a> | <a href="#">CRL2512-JV-R024E</a> | <a href="#">CRL2512-FU-R020E</a> | <a href="#">CRL2512-JU-R020E</a> |
| <a href="#">CRL2010-FU-R016E</a> | <a href="#">CRL2512-JW-R510E</a> | <a href="#">CRL2512-FW-R510E</a> | <a href="#">CRL0805-FW-R082E</a> | <a href="#">CRL2010-FU-R011E</a> |
| <a href="#">CRL0805-JW-R082E</a> | <a href="#">CRL2010-FU-R018E</a> | <a href="#">CRL2512-FW-R750E</a> | <a href="#">CRL2512-JW-R750E</a> | <a href="#">CRL1206-FW-R300E</a> |
| <a href="#">CRL1206-JW-R300E</a> | <a href="#">CRL2010-FU-R012E</a> | <a href="#">CRL2512-FW-R082E</a> | <a href="#">CRL2512-JW-R082E</a> | <a href="#">CRL2512-JW-R220E</a> |