




LOC	DIST	REVISIONS				
CM	00	P	LTR	DESCRIPTION	DATE	DWN APVD
			DI	REVISED PER ECO-11-005027	14MAR2011	RK HMR

- 1

0.000762 THK GOLD STRIPE IN THE GOLD PLATE AREA, BRIGHT TIN IN THE CRIMP AREA, OVER NICKEL PLATE.
- 2

0.000381 THK GOLD STRIPE IN THE GOLD PLATE AREA, BRIGHT TIN IN THE CRIMP AREA, OVER NICKEL PLATE.
- 3

0.0015 - 0.0040 THK BRIGHT TIN.
- 4

WIRE RANGE: 20 - 24 AWG.
- 5

INSULATION RANGE 0.89 - 1.524.
- 7

0.000762 THK GOLD STRIPE IN THE GOLD PLATE AREA, BRIGHT TIN-LEAD IN THE CRIMP AREA, OVER NICKEL PLATE.
- 8

0.000381 THK GOLD STRIPE IN THE GOLD PLATE AREA, BRIGHT TIN-LEAD IN THE CRIMP AREA, OVER NICKEL PLATE.

SECTION C-C
SCALE 20:1

SECTION B-B
SCALE 20:1

SECTION A-A
SCALE 20:1

3 DIMENSIONAL VIEW
SCALE 8:1

1	I-794610-2
2	I-794610-1
7	794610-3
8	794610-2
3	794610-1
FINISH	PART NUMBER

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 19-OCT-1999	STE TE Connectivity			
DIMENSIONS: mm		CHK K. COBLE 19-OCT-1999				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. COBLE 19-OCT-1999	NAME CONTACT, RECEPTACLE, CRIMP, SNAP-IN, LOOSE PIECE, MICRO MATE-N-LOK(TM)			
0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±0.30° FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	SIZE A200779	CAGE CODE C-794610	DRAWING NO - RESTRICTED TO	-
MATERIAL 0.2 PH BRZ		SEE TABLE	CUSTOMER DRAWING			
			SCALE 10:1	SHEET 1	OF 1	REV DI