






PRODUCT NO.
10018784-X0XXXX



SECTION P-P





PLASTIC PEG TYPE

CONFIDENTIAL


mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		A FCI www.fciconnect.com												
ltr	ecn no		dr	date	linear	.X ± 0.30				projection	title PCI EXPRESS GEN3  CARD EDGE ASSY											
M	T05-0124		M W	06/07/05		.XX ± 0.20																
N	T05-0153		M W	07/12/05		.XXX ± 0.10																
P	T05-0208		M W	09/15/05		0° ±2°																
R	T06-0206		R C	12/01/06	dr	STONE LI		05/27/15		 MM	product family					EDGE CARD					code	
S	ELX-DG-21161-1		S T	05/27/15	engr	STONE LI		05/27/15			size					dwg no					TWN	
					chr	/		/		scale	A4					10018784					sheet 1 of 6	
					appd	PM ZHENG		05/27/15														
sheet index		revision		S	S	S	S	S	S													
		sheet		1	2	3	4	5	6													

PRODUCT NO.
10018784-X1XXXX



METAL BOARD LOCKS TYPE

CONFIDENTIAL



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI		www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 0.30	projection	title	product family	EDGE CARD	code	
				angles	.XX ± 0.20	MM	PCI EXPRESS GEN3 CARD EDGE ASSY	size	dwg no	TWN	
				dr	.XXX ± 0.10	scale				sheet	
				enr	0° ±2°	2:1				2 of	
				chr	STONE LI 05/27/15						
				appd	STONE LI 05/27/15						
					/						
					PM ZHENG 05/27/15						
sheet index	revision sheet										


cage code
22526



CONFIDENTIAL

[illegible]

	cage code
	22526



 I/O PANEL DIRECTION
 PRIMARY (COMPONENT) SIDE



CONFIDENTIAL

[illegible]

PDS: Rev :S ACAD STATUS:Released Printed: Jul 09, 2015

NOTES:

1.MATERIAL:

HOUSING: NYLON, GLASS FILLED UL94V-0 RATE, SUITABLE FOR WAVE SOLDERING.

TERMINAL: COPPER ALLOY

PLATING: 50u" NICKEL UNDERPLATE ALL OVER

CONTACT AREA PLATING - SEE PRODUCT NUMBER CODE

SOLDER TAIL: TIN/LEAD (90/10) - SEE PRODUCT

NUMBER CODE 100u" MIN. OVER 50u" NICKEL

METAL BOARD LOCKS: COPPER ALLOY

FINISH: 100u" TIN/LEAD (90/10) OVER 50u" NICKEL

UNDERPLATE SEE PRODUCT NUMBER CODE

2.PRODUCT SPECIFICATION: GS-12-233

③THE HORIZONTAL AXIS FOR THE HOLE PATTERN IS ESTABLISHED BY

A LINE THROUGH THE CENTER OF THE TWO Ø2.35 HOLES.

THE VERTICAL AXIS IS 90° TO THE HORIZONTAL AXIS, THROUGH THE CENTER OF DATUM Z.

④NO TIE BAR PERMITTED FROM CARD EDGE TO LEADING EDGE OF PAD FOR

PINS A1 AND PIN NUMBERS "F".

⑤CHAMFER EDGES MUST BE FREE OF CUTTING BURRS.

⑥FREQUENCY & LOCATION AT SUPPLIER DISCRETION. RIDGE MAY BE

CONTINUOUS WITH NO BREAKS.

7.RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2um MINIMUM MATTE TIN OVER 1.27um MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.

- THE HOUSING WILL WITHSTAND EXPOSURE TO 240°C±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.(For 10018784-X 0 X X X X(X X) options)

CONNECTOR	# POS REF.	N	DIM "A"	DIM "B"	DIM "C"	"E"
1 PORT	36	6	7.65	25.00	9.15	6.00
4 PORT	64	20	21.65	39.00	23.15	20.00
8 PORT	98	37	38.65	56.00	40.15	37.00
16 PORT	164	70	71.65	89.00	73.15	70.00

PRODUCT NUMBER CODE
10018784-X X X X X X □ □

HOUSING COLOR OPTIONS

0-WHITE
1-BLACK

LEAD FREE OPTION

LEAVE BLANK FOR TERMINAL PLATING 3,4,5
"LF" FOR TERMINAL PLATING OPTION 0,1,2

PACKAGING OPTIONS

T-TRAY PACKAGING

M-TRAY PACKAGING & MYLAR TAPE FOR PICK-N-PLACE. SEE FIGURE 1

PEGS OPTIONS

0-PLASTIC PEGS
1-METAL BOARD LOCKS

POS OPTIONS

0-36
1-64
2-98
3-164


TERMINAL PLATING OPTIONS

TAIL LENGTH OPTIONS

0-50u" Ni UNDERPLATE
30u" Au CONTACT AREA
100u" TIN TAIL AREA ----- COMPATIBLE RoHS
1-50u" Ni UNDERPLATE
15u" Au CONTACT AREA
100u" TIN TAIL AREA ----- COMPATIBLE RoHS
2-50u" Ni UNDERPLATE
GOLD FLASH CONTACT AREA
100u" TIN TAIL AREA ----- COMPATIBLE RoHS
3-50u" Ni UNDERPLATE
30u" Au CONTACT AREA
100u" TIN/LEAD TAIL AREA ----- INCOMPLIANT RoHS
4-50u" Ni UNDERPLATE
15u" Au CONTACT AREA
100u" TIN/LEAD TAIL AREA ----- INCOMPLIANT RoHS
5-50u" Ni UNDERPLATE
GOLD FLASH CONTACT AREA
100u" TIN/LEAD TAIL AREA ----- INCOMPLIANT RoHS

	DIM "D"	PCB THICKNESS	BOARD LOCKS DIM"G"
0	2.30 ^{+0.25} _{-0.13}	1.56±0.10	1.70±0.15
1	3.10 ^{+0.25} _{-0.13}	2.36±0.10	2.50±0.15

CONFIDENTIAL

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com			
ltr	ecn no	dr	date	linear	.X ±			projection		title	PCI EXPRESS GEN3 CARD EDGE ASS'Y 		
					.XX ±								
					.XXX ±								
				angles	0° ±2°			MM		product family	EDGE CARD		code
					dr	STONE LI	05/27/15				size	dwg no	
				enrg	STONE LI	05/27/15	scale	1:1	A4	10018784	sheet 5 of		
				chr	/	/							
				appd	PM ZHENG	05/27/15							
sheet index	revision												
	sheet												

cage code
22526







FIGURE 1

CONFIDENTIAL

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com			
ltr	ecn no	dr	date	linear	.X ± 0.25					
					.XX ± 0.13					
					.XXX ± 0.05					
				angles	0° ± 2°	 MM	 MM		 MM	
				dr	STONE LI 05/27/15					
				enr	STONE LI 05/27/15					
				chr	/ /					
				appd	PM ZHENG 05/27/15					
sheet index		revision sheet								

CUSTOMER COPY

FCI

www.fciconnect.com

projection

MM

scale 1.5:1

title PCI EXPRESS GEN3 CARD EDGE ASS'Y

product family EDGE CARD

size dwg no 10018784

code TWN sheet 6 of

cage code 22526