

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0901210122](#)  
**Status:** **Active**  
**Overview:** [C-Grid III™](#)  
**Description:** 2.54mm (.100") Pitch C-Grid III™ Header, Single Row, Right Angle, 2 Circuits, Tin (Sn) Plating

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

Product Family PCB Headers  
Series [90121](#)  
Application Wire-to-Board  
Overview [C-Grid III™](#)  
Product Name C-Grid III™

**Physical**


Breakaway Yes  
Circuits (Loaded) 2  
Circuits (maximum) 2  
Color - Resin Black  
First Mate / Last Break No  
Glow-Wire Compliant No  
Guide to Mating Part No  
Keying to Mating Part None  
Lock to Mating Part None  
Material - Metal Brass  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Material - Resin Polyester  
Number of Rows 1  
Orientation Right Angle  
PC Tail Length (in) 0.114 In  
PC Tail Length (mm) 2.90 mm  
PCB Locator No  
PCB Retention None  
Packaging Type Bag  
Pitch - Mating Interface (in) 0.100 In  
Pitch - Mating Interface (mm) 2.54 mm  
Plating min: Mating (µin) 160  
Plating min: Mating (µm) 4.00  
Plating min: Termination (µin) 120  
Plating min: Termination (µm) 3  
Polarized to Mating Part No  
Polarized to PCB No  
Shrouded No  
Stackable No  
Temperature Range - Operating -55°C to +125°C  
Termination Interface: Style Through Hole

**Electrical**

Current - Maximum 3A  
Voltage - Maximum 350V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 5



Series image - Reference only

**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC**  
**Contains SVHC: No**  
**Halogen-Free  
Status**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**  
[90121 Series](#)

|                                         |                        |
|-----------------------------------------|------------------------|
| Lead-free Process Capability            | Wave Capable (TH only) |
| Max. Cycles at Max. Process Temperature | 1                      |
| Process Temperature max. C              | 260                    |

**Material Info**

**Reference - Drawing Numbers**

|               |           |
|---------------|-----------|
| Sales Drawing | SDA-90121 |
|---------------|-----------|

This document was generated on 12/08/2009

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**