


SWITCHING REGULATOR APPLICATION.
HIGH VOLTAGE SWITCHING APPLICATION.
HIGH SPEED DC-DC CONVERTER APPLICATION.

FEATURES

- Excellent Switching Times
: $t_{on}=1.6\ \mu s$ (Max.), $t_f=0.7\ \mu s$ (Max.), at $I_C=5A$
- High Collector Voltage : $V_{CBO}=700V$.

MAXIMUM RATING ($T_a=25\ ^\circ C$)

CHARACTERISTIC		SYMBOL	RATING	UNIT
Collector-Base Voltage		V_{CBO}	700	V
Collector-Emitter Voltage		V_{CEO}	400	V
Emitter-Base Voltage		V_{EBO}	9	V
Collector Current	DC	I_C	8	A
	Pulse	I_{CP}	16	
Base Current		I_B	4	A
Collector Power Dissipation ($T_c=25\ ^\circ C$)		P_C	80	W
Junction Temperature		T_j	150	
Storage Temperature Range		T_{stg}	-55 150	

ELECTRICAL CHARACTERISTICS ($T_a=25\ ^\circ C$)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Emitter Cut-off Current	I_{EBO}	$V_{EB}=9V, I_C=0$	-	-	1	mA
DC Current Gain	$h_{FE}(1)$ (Note)	$V_{CE}=5V, I_C=2A$	15	-	39	
	$h_{FE}(2)$	$V_{CE}=5V, I_C=5A$	10	-	-	
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C=2A, I_B=0.4A$	-	-	1	V
		$I_C=5A, I_B=1A$	-	-	2	
		$I_C=8A, I_B=2A$	-	-	3	
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C=2A, I_B=0.4A$	-	-	1.5	V
		$I_C=5A, I_B=1A$	-	-	1.6	
Collector Output Capacitance	C_{ob}	$V_{CB}=10V, f=0.1MHz, I_E=0$	-	110	-	pF
Transition Frequency	f_T	$V_{CE}=10V, I_C=0.5A$	4	-	-	MHz
Turn-On Time	t_{on}	$I_{B1}=I_{B2}=1A$ DUTY CYCLE $\leq 2\%$	-	-	1.6	μs
Storage Time	t_{stg}		-	-	3	μs
Fall Time	t_f		-	-	0.7	μs

Note : h_{FE} Classification R:15 27, O:23 39

