

CM2500 Series


Single Phase Bridge Rectifiers



Features:

- Metal case for maximum heat dissipation.
- Surge overload ratings to 400 amperes.

CM Series



Diameters : Inches (Millimetres)



CM2500 Series

Single Phase Bridge Rectifiers



Mechanical Data :

Case : Metal.
Mounting position : Any.

Maximum Rating and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

Parameter	CM2500	CM2501	CM2502	CM2504	CM2506	CM2508	CM25010	Unit
Maximum recurrent peak reverse voltage	50	100	200	400	600	800	1000	V
Maximum RMS bridge input voltage	35	70	140	280	420	560	700	
Maximum DC blocking voltage	50	100	200	400	600	800	1000	
Maximum average forward current at T _A = 55°C	25							A
Non-repetitive peak forward surge current, rated load	300							
Maximum forward voltage per bridge element specified current at 12.5A	1.2							V
Maximum reverse current at rated DC blocking voltage per element	10							μA
I ² t rating for fusing (t <8.35ms)	374							A ² S
Typical thermal resistance RθJC	2.5							°C/W
Operating temperature range T _J	-55 to +150							°C
Storage temperature range T _A								

Note : * Unit mounted on metal heat-sink.




CM2500 Series




Single Phase Bridge Rectifiers

Ratings and Characteristic Curves


Output Current VS. Case Temperature Resistive
Or Inductive Load $T_J = 150^\circ\text{C}$




Typical Instantaneous Forward
Characteristics at $T_J = 25^\circ\text{C}$



Output Current VS. Ambient Temperature Resistive
or Inductive Load Bridge Mounted on 8 x 8 inches
Aluminium Plate 25 inches Thick



Power Dissipation VS. Average Output Current
Resistive or Inductive Load $T_J = 150^\circ\text{C}$



CM2500 Series

Single Phase Bridge Rectifiers



Specifications

Current Rating (A)	VRRM (V)	Maximum AC Input Voltage (V)	Part Number
25	50	35	CM2500
	100	70	CM2501
	200	140	CM2502
	400	280	CM2504
	600	420	CM2506
	800	500	CM2508
	1000	800	CM25010

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

