

Specification Status : Released

Electrical Rating

Voltage: 20V MAX
Current: 100A MAX

Chip Size: 14 x 17.5mm

Leads: Nickel 1/4H
0.125mm nominal thickness

Tape: Polyester (White)
18.5mm Width

Solder: Lead-free

Lot Marking Ink Color (Green)

Marking:

— Manufacturer's Mark
XX E73 — Part Identification
□□□□ — Lot Identification




TABLE I. DIMENSIONS:

	A		B		C		D		E		F		G	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
Mm:	27.1	29.1	13.9	14.5	0.6	1.0	4.1	5.5	4.1	5.5	5.9	6.1		
In*:	(1.07)	(1.15)	(0.55)	(0.57)	(0.02)	(0.04)	(0.16)	(0.22)	(0.16)	(0.22)	(0.23)	(0.24)		

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS: As measured in Muller Kelvin Clips Model BU-75K.

I HOLD	CURRENT TRIP LIMITS								TIME TO TRIP		REFERENCE RESISTANCE		ONE-HOUR POST-TRIP RESISTANCE		TRIPPED-STATE POWER DISSIPATION	
	AMPS AT 0°C		AMPS AT 20°C		AMPS AT 60°C		AMPS AT --°C									
AMPS 20°C HOLD	HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	SECONDS AT 20°C, 30.0A TYP	MAX	OHMS AT 20°C MIN	MAX	OHMS AT 20°C MIN	MAX	WATTS AT 20°C, 20V TYP	MAX
7.3	8.6	16.6	7.3	14.1	5.4	10.5	--	--	--	5	0.006	0.012	0.006	0.015	--	3.3

Agency Recognitions:
Reference Documents:
Precedence:
Effectivity:
CAUTION:

UL, TUV, CSA
PS300

This specification takes precedence over documents referenced herein.

Reference documents shall be the issue in effect on the date of invitation for bid.

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.