

NUMBER  
917658

3rd ANGLE PROJECTION

METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

キーイング位置: 表参照  
KEYING LOCATION: SEE TABLE

タブコンタクト  
TAB CONTACT

キーイング表示: 表参照  
KEYING ID: SEE TABLE

AMPマーク  
シリーズマーク  
D/C  
回路番号  
CIRCUIT NO

39.4

7.62

16.97

5.08

5.08×5=25.4

5.08

21.6

3.8

3.175

5.08

5.08×5=25.4

リテンションレグ  
RETENTION LEG

コンタクト半田付部  
CONTACT TAIL

コネクタ外形  
OUTLINE OF HEADER HOUSING

12-φ1.1  
DIA 1.1±0.1 12 PLACES

スルーホール 2-φ2  
DIA 2±0.1 2 PLACES

ラウンド 2-φ3MIN  
ROUND DIA 3MIN 2 PLACES

7.62

1.27

31.75

3.175

1.27

7.62

16.97

12.47

5.08

5.08×5=25.4

39.4

7

推奨基板取付け寸法  
PC 基板厚: 1.6±0.1  
(非累積公差)  
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN  
PC BOARD THICKNESS: 1.6±0.1  
(NOT ACCUMULATE TOLERANCE)  
(CONNECTOR MOUNT SIDE)

NOTES

1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER (94V-0), COLOR: BLACK  
CONTACT: COPPER ALLOY  
RETENTION LEG: COPPER ALLOY

△2. FINISH (CONTACT AREA): 0.38μm MIN GOLD PLATING OVER Ni PLATING

△3. FINISH (CONTACT AREA): 0.76μm MIN GOLD PLATING OVER Ni PLATING

△4. FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL

△5. FINISH (RETENTION LEG): TIN-LEAD PLATED (CONTACT TAIL) OVER NICKEL

△6. FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

注記

1. 材料: ハウジング: ガラス入り熱可塑性ポリエステル樹脂 (94V-0), 色: 黒  
コンタクト: 銅合金  
リテンションレグ: 銅合金

△2. めっき: コンタクト: 全面Ni下地  
接触部: 0.38μm MIN 金めっき

△3. めっき: コンタクト: 全面Ni下地  
接触部: 0.76μm MIN 金めっき

△4. めっき: コンタクト: 全面Ni下地  
接触部: 2.0 μm MIN スズめっき

△5. めっき: リテンションレグとコンタクト半田付部  
ニッケル下地の土に半田めっき

△6. めっき: リテンションレグとコンタクト半田付部  
ニッケル下地の土にスズめっき

|       |  |   |   |       |            |
|-------|--|---|---|-------|------------|
| A ROW |  | X | Y | △6 △4 | 3-917658-5 |
| B ROW |  |   |   | △6 △3 | 3-917658-3 |
| A ROW |  | Y | Y | △6 △2 | 3-917658-2 |
| B ROW |  |   |   | △6 △4 | 2-917658-5 |
| A ROW |  |   |   | △6 △3 | 2-917658-3 |
| B ROW |  |   |   | △6 △2 | 2-917658-2 |
| A ROW |  | X | X | △6 △4 | 1-917658-5 |
| B ROW |  |   |   | △6 △3 | 1-917658-3 |
|       |  |   |   | △6 △2 | 1-917658-2 |

|                 |  |              |              |        |      |          |
|-----------------|--|--------------|--------------|--------|------|----------|
| KEYING LOCATION |  | A ROW KEYING | B ROW KEYING | FINISH | 製品番号 | PART NO. |
|                 |  |              |              |        |      |          |

TE Connectivity

|                           |                           |                                                                        |                             |       |          |
|---------------------------|---------------------------|------------------------------------------------------------------------|-----------------------------|-------|----------|
| WIRE RANGE                | INSULATION DIA            | NAME                                                                   |                             |       |          |
| mm (AWG)                  | mm                        | ダイナミック D-3200 垂直タイプ 12 極<br>ヘッダーアセンブリー                                 |                             |       |          |
| MATERIAL                  | FINISH                    | DYNAMIC D-3200 12 POS. V-HDR ASS'Y                                     |                             |       |          |
| SEE NOTE<br>注記参照          | SEE NOTE<br>注記参照          | 一般公差<br>(GENERAL TOLERANCE)                                            | SIZE                        | LOC   | NUMBER   |
| DR. 24/APR/95<br>K. IKEDA | DE. 24/APR/95<br>K. IKEDA | 10mm以下: ±0.3<br>10mm以上30mm以下: ±0.4<br>30mm以上100mm以下: ±0.45<br>角 度: ±3' | A3                          | J     | C-917658 |
| LTR                       | REVISION RECORD           | DR. 24/APR/95<br>S. MANABE                                             | APP. 24/APR/95<br>S. MANABE | SCALE | REV.     |
|                           |                           |                                                                        |                             | 2-1   | C1       |

|     |                           |    |     |         |
|-----|---------------------------|----|-----|---------|
| C1  | REVISED PER ECO-11-005030 | RK | HMR | 23MAR11 |
| LTR | REVISION RECORD           | DR | CHK | DATE    |