









**SPECIFICATIONS:****1. Material:**

(1). Screw: C1010.

(2). Body: PA66

(3). Terminal: Brass

(4). cage: Brass

(5). Cover: PA66

2. Wire range: 22 - 14AWG.

3. Electrical rating: 300V, 15A.

4. MAX TORQUE: 4.5 in-lbs.

5. Wire strip length: 5.00mm.

8. Insulation resistance: DC500V, 500M.

9. Operating temperature: -40C to +105C.

10. A = N x P.

11. B = (N - 1) x P

12. P = (Pitch) = 5.00MM (.197").

13. N = Number of positions available 2 through 24.

(B) 14. ALL COMPONENTS ARE ROHS COMPLIANT.

ADDED DIM. & ROHS NOTE
EC NO: ETC2007-0156
2006/10/11
DRW: NEHLE
2006/10/11
CHKD: JMACNEIL
2006/10/12
APPR: JMACNEIL

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± .0015
3 PLACES	± 0.038	± .005
2 PLACES	± 0.13	± .01
1 PLACE	± 0.3	± ---
ANGULAR ± 2 °		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
LROTHAUS	12/6/05
CHECKED BY	DATE
C. YORK	01/06/06
APPROVED BY	DATE

MATERIAL NO.
SEE CHART

SCALE
4:1

DESIGN UNITS
INCH

THIRD ANGLE PROJECTION

TITLE
5.0MM, EURO TERM BLOCK
VERTICAL, PC MOUNT
STAMPED TERMINAL

MOLEX INCORPORATED

DOCUMENT NO.
SD-39543-005

SHEET NO.
1 OF 1

