

DC Fan Motors
CPU coolers

 **66×62mm**
SAN ACE MC



Directly cools CPU, integral with a heat sink

General specifications


Life expectancy	40,000 hours
	(survival rate: 90% at 60°C, rated voltage, and continuously run in a free air state)
Motor protection system	Current cut system (with reverse-connection protection)
Dielectric strength	50/60 Hz, 500 VAC, 1 minute (between input terminal and frame)
Operating thermally range	- 10°C to + 70°C (non-condensing)
Heat resistance	As per Sanyo Denki's measurement method

30mm thick

Specifications

Model No.	Rated voltage (V)	operating voltage range (V)	Rated current (A)	Rated input (W)	Rated rotating speed (min ⁻¹)	Thermal resistance (K/W)	Noise (dB [A])	Mass (g)
109P6605H2026	5	4.5 to 5.5	0.2	1	3,600	0.79	29	126
109P6612H2026	12	7 to 13.8	0.08	0.96				

Typical cooling characteristics




109P6605H2026
109P6612H2026


CPU Cooler

 **66×62mm**

Dimensions (unit: mm)



Relay harness



Installation metal fittings (unit : mm)

