









SET INSTALLTION OF PCB & CHASSIS OR HEATSINK

NOTE

1. MATERIAL


- HEADER : LIQUID CRYSTAL POLYMER(LCP)
UL94V-0, HALOGEN FREE, COLOR OF NATURAL
- CONTACT TERMINAL : COPPER-ALLOY, 0.3mm THICKNESS

2. PLATING



- CONTACT TERMINAL : TIN -PLATED
0.8μm MINIMUM TIN PLAING

3. PRODUCT SPECIFICATION : RPS-104266-001


- 4. PACKAGING SPECIFICATION : PK-104266-001
- 5. COPLANALITY OF SOLDER TAILS (PEAK TEMP. : 260°C),
BEFORE & AFTER REFLOW : 0.08 MAX.
- 6. APPLICABLE SOLIDE WIRE RANGE :
(OUTSIDE WIRE INSULATION : 2.1mm DIAMETER MAX.)
 - SOLID WIRE : AWG #24~#18
 - STRAND WIRE : AWG #24~#20




QUALITY SYMBOLS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	=	0	2017/07/20 2017/08/08 2017/08/08	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS		SCALE		molex® LITE TRAP CONN. BOTTOM ENTRY TYPE HEADER ASS'Y 2CKTS							
	=	0			MM		5:1									
	=	0			DRWN BY		DATE									
					SCHONG03		2016/02/20									
	=	0			CHK'D BY		DATE									
					SHCHU		2016/02/20									
	=	0	EC NO: 120165 DRWN: JSSHIN CHK'D: SHCHU APPR: YSKIM02	ANGULAR TOL ± 3.0 °	4 PLACES		±		PRODUCT CUSTOMER DRAWING							
	=	0			3 PLACES		±									
	=	0			2 PLACES		± 0.15									
					1 PLACE		± 0.2									
	=	0			0 PLACES		±									
	=	0			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		YSKIM02							2016/03/03		
	=	0			DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER			
					A3				104266		1042660210		GENERAL MARKET			
	=	0	B	REV			DOCUMENT NUMBER				DOC TYPE		DOC PART		SHEET NUMBER	
							SD-104266-003				PSD		001		1 OF 2	




SECTION A-A




SECTION B-B



PULL OUT
DIRECTION




PLASTIC BOBBIN




NOTES

1. NUMBER OF CONNECTORS : 700 PCS/REEL.
2. LEAD TAPE LENGTH.



3. PEEL-OFF FORCE OF TOP TAPE : 0.1N~0.59N (10.2gf~60gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
<PEEL-OFF SPEED : 300mm/min (REF.)>



4. FLASH IN ANY PORTION SHOULD BE LESS THAN 0.20mm MAX.
5. UNLESS OTHERWISE SPECIFIED INNER R0.2 MAX

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®			
▽A	= 0	ANGULAR TOL ± 3.0 °		MM		2:1					
▽E	= 0	4 PLACES	±	DRWN BY	DATE			LITE TRAP CONN. BOTTOM ENTRY TYPE HEADER ASS'Y 2CKTS			
▽F	= 0	3 PLACES	±	SCHONG03	2016/02/20						
▽P	= 0	2 PLACES	± 0.2	CHK'D BY	DATE			PRODUCT CUSTOMER DRAWING			
▼	= 0	1 PLACE	± 0.2	SHCHU	2016/02/20						
▽C	= 0	0 PLACES	±	APPR BY	DATE			SERIES	MATERIAL NUMBER	CUSTOMER	
⊠	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		YSKIM02	2016/03/03			104266	1042660210	GENERAL MARKET	
■	= 0			DRAWING SIZE	THIRD ANGLE PROJECTION			DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
▽	= 0			A3				SD-104266-003	PSD	001	2 OF 2